

# ULTRA MINIATURE CERAMIC GLASS SEALED SMD CRYSTAL



3.2 x 2.5 x 1.0mm

**ABM8G**

Pb in glass exemption 7 (c)-I per  
RoHS II 2011/65/EU Annex

RoHS/RoHS II Compliant

**Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable**

➤ **FEATURES:**

- Low in height; suitable for thin equipment
- Glass sealed package assures high reliability and high temperature operation
- Tight tolerance and stability available
- IR reflow capable
- Low cost version of ABM8 crystal


➤ **APPLICATIONS:**

- High density applications.
- Modems, communication and test equipment.
- PCMCIA, wireless applications

➤ **STANDARD SPECIFICATIONS:**

| Parameters                                                         | Minimum     | Typical | Maximum | Units | Notes                 |
|--------------------------------------------------------------------|-------------|---------|---------|-------|-----------------------|
| Frequency Range                                                    | 12.000      |         | 50.000  | MHz   |                       |
| Operation Mode                                                     | Fundamental |         |         |       |                       |
| Operating Temperature                                              | -10         |         | +60     | °C    | See options           |
| Storage Temperature                                                | -40         |         | +85     | °C    |                       |
| Frequency Tolerance @+25°C                                         | -50         |         | +50     | ppm   | See options           |
| Frequency Stability over the Operating Temperature (ref. to +25°C) | -50         |         | +50     | ppm   | See options           |
| Equivalent series resistance                                       |             |         | 120     | Ω     | 12.000MHz             |
|                                                                    |             |         | 80      |       | 12.001MHz ~ 20.000MHz |
|                                                                    |             |         | 60      |       | 20.001MHz ~ 28.000MHz |
|                                                                    |             |         | 50      |       | 28.001MHz ~ 50.000MHz |
| Shunt capacitance (C0)                                             |             |         | 5.0     | pF    |                       |
| Load capacitance (CL)                                              | 10          |         |         | pF    | See options           |
| Drive Level                                                        |             | 10      | 100     | μW    |                       |
| Aging@25°C±3°C                                                     |             |         | ±3      | ppm   | First year            |
| Insulation Resistance                                              | 500         |         |         | M Ω   | @ 100Vdc ± 15V        |

➤ **OPTIONS & PART IDENTIFICATION:**



# ULTRA MINIATURE CERAMIC GLASS SEALED SMD CRYSTAL




3.2 x 2.5 x 1.0mm

ABM8G

Pb in glass exemption 7 (c)-I per  
RoHS II 2011/65/EU Annex


RoHS/RoHS II Compliant

## OUTLINE DRAWING:




## TAPE & REEL:

Tape and reel (1,000pcs/reel)  
Tape and reel (3,000pcs/reel)



## REFLOW PROFILE:



Need a test socket for the ABM8G Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#).

**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO 9001 : 2008  
CERTIFIED



2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 08.13.15**  
Ph. 949.546.8000 | Fax. 949.546.8001  
Visit [www.abracon.com](http://www.abracon.com) for Terms and Conditions of Sale