






Copyright FCI.

PRODUCT NUMBER
70430-XYX
70430-XYXLF



PLATING IN CONTACT AREA

DASH NUMBER	PERFORMANCE LEVEL
-1YY	TELCORDIA CO & IEC CLASS I
-2YY	TELECOM CLASS
-3YY	TELCORDIA CO & IEC CLASS I
-5YY	TELCORDIA UE
-1YYLF	TELCORDIA CO & IEC CLASS I
-2YYLF	TELECOM CLASS
-5YYLF	TELCORDIA UE



NOTES:

- FOR DIM A, AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL
PHOSPHOR BRONZE:
- PLATING ON PRESS-FIT TAIL:
70430-XYX IS SnPb
70430-XYXLF IS Sn (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION J& BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES. IF TRAY PACKAGING IS REQUIRED, SUFFIX "P" WILL BE ADDED TO THE END OF THE PART NUMBER. EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION: GS-12-180
APPLICATION SPECIFICATION: BUS-20-075
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

rev	ecn no	dr	date
AW	DG-006740-1	TER	2011-10-08
AR	V06-0948	DCH	2006-09-12
AS	DG09-0256	TER	2009-08-19
AT	DG09-0366	TER	2009-11-24
AU	DG10-0002	TER	2010-01-05
AV	DG-003807-1	TER	2011-05-11

spec ref		*		dr		Terran Huang		2010/07/08		projection				mm		size		A4		scale		11:10																					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Terran Huang		2011/10/09				ecn no		ELX-DG-006740-1																											
						chr		Tao Huang		2011/10/18																																	
						appr		Pei-Ming Zheng		2011/10/18																																	
						product family						METRAL						rel level						Released																			
surface		3.200 linear		0.X		±0.3				title		METRAL POWER HEADER						dwg no		70430						rev																	
				0.XX		±0.13																																					
				0.XXX		±0.051																																					
		angular		0°		±2°		www.fci.com																				cat. no.		-		Product - Customer Drw						sheet 1 of 6					

Print File - REV C - 2009-06-09


PDS: Rev :AW

STATUS:Released

Printed: Oct 18, 2011



Copyright FCI.



KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.30
P02	7.25	4.30
P03	8.00	4.30
P04	6.50	13.60
P05	7.25	13.60
P06	8.00	13.60
P07	6.5	17.00
P08	7.25	17.00
P11	7.25	12.20
P12	8.00	12.20
P16	5.00	4.30
P17	5.75	4.30
P29	7.25	11.80

REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

spec ref		*		dr	Terran Huang	2010/07/08	projection	mm	size	A4	scale	21:10	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Terran Huang	2011/10/09			ecn no	ELX-DG-006740-1			
				chr	Tao Huang	2011/10/18							
				appr	Pei-Ming Zheng	2011/10/18							product family
surface	3.200 linear	0.X	±0.3		title	METRAL POWER HEADER			dwg no	70430		rev	AV
		0.XX	±0.13										
		0.XXX	±0.051										
	angular	0°	±2°										



Copyright FCI.


A	METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
			I	2			I	2			I	2			I	2			I	2
			E	-			E	P03			E	P01			E	P01			E	P03
			D	P03			D	P03			D	P01			D	P01			D	P03
			C	P02			C	P03			C	P03			C	P03			C	-
B	METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
			I	2			I	2			I	2			I	2			I	2
			E	P01			E	P03			E	P01			E	P01			E	P01
			D	P02			D	P02			D	P01			D	P01			D	P01
			C	P03			C	P01			C	P02			C	-			C	P01
C	METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
			I	2			I	2			I	2			I	2			I	2
			E	P02			E	P01			E	P06			E	P06			E	P02
			D	-			D	-			D	P06			D	P01			D	P01
			C	P01			C	-			C	P06			C	P01			C	P01
D	METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I		METRAL P/N	ROW	CONTACT CODE MOD. I	
			I	2			I	2			I	2			I	2			I	2
			E	P02			E	P03			E	P03			E	P03			E	P05
			D	P03			D	-			D	P02			D	P03			D	P05
			C	-			C	P03			C	P03			C	P03			C	P05


spec ref *				dr Terran Huang		2010/07/08		projection	mm	size	A4	scale	11:10
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Terran Huang		2011/10/09				ecn no	ELX-DG-006740-1		
				chr Tao Huang		2011/10/18							
				appr Pei-Ming Zheng		2011/10/18							
				product family				METRAL		rel level		Released	
surface 3.2	linear	0.X	±0.3		title METRAL POWER HEADER				dwg no	70430		rev	AV
		0.XX	±0.13										
		0.XXX	±0.051										
	angular	0°	±2°	www.fci.com		cat. no.		-		Product - Customer Drw			



Copyright FCI.

1				2				3				4							
METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I	
			I	2				I	2				I	2				I	2
70430-X21 SEE NOTE 4 FOR LEAD-FREE CODE		E	P02	P02	70430-X25 SEE NOTE 4 FOR LEAD-FREE CODE		E	P04	P06	70430-X29 SEE NOTE 4 FOR LEAD-FREE CODE		E	P04	P05	70430-X33 SEE NOTE 4 FOR LEAD-FREE CODE		E	P02	-
		D	P02	P02			D	P04	P06			D	P05	P05			D	P02	-
		C	P02	P02			C	P04	P06			C	P05	P05			C	P02	-
		B	P02	P02			B	P04	P06			B	P05	P05			B	P02	-
		A	P03	P03			A	P04	P06			A	P05	P05			A	P02	-
METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I	
			I	2				I	2				I	2				I	2
70430-X22 SEE NOTE 4 FOR LEAD-FREE CODE		E	P06	P06	70430-X26 SEE NOTE 4 FOR LEAD-FREE CODE		E	P03	P03	70430-X30 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P02	70430-X34 SEE NOTE 4 FOR LEAD-FREE CODE		E	P02	-
		D	P06	P06			D	P02	P02			D	-	P01			D	-	P01
		C	P06	P05			C	P01	P01			C	P02	P02			C	P02	-
		B	P06	P05			B	-	-			B	P02	P02			B	-	P01
		A	P06	P06			A	P03	-			A	P02	P02			A	P02	-
METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I	
			I	2				I	2				I	2				I	2
70430-X23 SEE NOTE 4 FOR LEAD-FREE CODE		E	P03	P03	70430-X27 SEE NOTE 4 FOR LEAD-FREE CODE		E	P06	P04	70430-X31 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P01	70430-X35 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P02
		D	P03	P03			D	P06	P06			D	P01	P01			D	P02	P01
		C	P03	P02			C	P06	P06			C	P01	P01			C	P01	P02
		B	P03	P02			B	P06	P06			B	P03	P01			B	P01	P01
		A	P03	P03			A	P06	P06			A	P03	P01			A	P02	P01
METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I	
			I	2				I	2				I	2				I	2
70430-X24 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P03	70430-X28 SEE NOTE 4 FOR LEAD-FREE CODE		E	P03	P01	70430-X32 SEE NOTE 4 FOR LEAD-FREE CODE		E	P05	P06	70430-X36 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P02
		D	P01	P03			D	P03	P03			D	P05	P06			D	P02	P01
		C	P01	P03			C	P03	P03			C	P05	P06			C	P01	P02
		B	P01	P03			B	P03	P03			B	P05	P06			B	P01	P01
		A	P01	P03			A	P03	P03			A	P05	P06			A	P02	P02
METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I		METRAL P/N		ROW	CONTACT CODE MOD. I	
			I	2				I	2				I	2				I	2
70430-X25 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P01	70430-X37 SEE NOTE 4 FOR LEAD-FREE CODE		E	P01	P02	70430-X40 SEE NOTE 4 FOR LEAD-FREE CODE		E	P03	P01					
		D	P01	P01			D	P03	P03			D	P03	P03					
		C	P02	P02			C	P03	P03			C	P03	P03					
		B	P01	P01			B	P03	P03			B	P03	P03					
		A	P02	P02			A	P03	P03			A	P03	P03					

spec ref *				dr Terran Huang 2010/07/08		projection		mm		size A4		scale 11:10			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Terran Huang 2011/10/09						ecn no ELX-DG-006740-1			
chr Tao Huang 2011/10/18						rel level Released									
appr Pei-Ming Zheng 2011/10/18						product family METRAL									
surface 3.2		linear		0.X ±0.3				title METRAL POWER HEADER 1 MOD, 5 ROW PRESS-FIT				dwg no 70430		rev AV	
				0.XX ±0.13											
				0.XXX ±0.051											
		angular		0° ±2°		www.fci.com		cat. no. -		Product - Customer Drw				sheet 4 of 6	

DC

1

2

3

4

A

METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2
70430-X61 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P01
	D	P01	P01
	C	P01	P01
	B	P01	P01
	A	-	-
70430-X65 SEE NOTE 4 FOR LEAD-FREE CODE	E	P02	P01
	D	P02	P02
	C	P02	P02
	B	P02	P02
	A	P02	P02



B

METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2
70430-X62 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P01
	D	P01	P01
	C	P01	P03
	B	P01	P01
	A	P01	P01
70430-X66 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01
	D	P03	P01
	C	P03	P03
	B	P03	P03
	A	P03	P03



C


METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2
70430-X63 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P02
	D	P03	P02
	C	P03	P03
	B	P03	P03
	A	P03	P03
70430-X67 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01
	D	P03	P03
	C	P02	P02
	B	P02	P02
	A	P02	P02



D

METRAL P/N	ROW	CONTACT CODE MOD. I	
		1	2
70430-X64 SEE NOTE 4 FOR LEAD-FREE CODE	E	P03	P01
	D	P03	P03
	C	P03	P02
	B	P03	P02
	A	P03	P02
70430-X68 SEE NOTE 4 FOR LEAD-FREE CODE	E	P01	P03
	D	P03	P03
	C	P02	P03
	B	P02	P03
	A	P02	P03



spec ref *				dr		Terran Huang	2010/07/08	projection		mm		size	A4	scale	11:10											
tolerance std				TOLERANCES UNLESS OTHERWISE SPECIFIED								eng	Terran Huang	2011/10/09	ecn no			ELX-DG-006740-1								
												chr	Tao Huang	2011/10/18												
								appr	Pei-Ming Zheng	2011/10/18	product family				METRAL				rel level				Released			
surface		3.200	linear	0.X	±0.3		title	METRAL POWER HEADER					dwg no	70430					rev	AW						
			0.XX	±0.13																						
			0.XXX	±0.051																						
		angular	0°	±2°	www.fci.com		cat. no.	-	Product - Customer Drw					sheet 6 of 6												

Print File - REV C - 2009-06-09

2

3

PDS: Rev :AW

STATUS:Released

Printed: Oct 18, 2011

A

B

C

D



Copyright FCI.