




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Insulator: Glass Filled Polyester
- Flammability: UL94V-0
- Color: Black

Ratings

- Operating Temperature:-40° - +105°
- RoHS Compliant

Circuits	Dimension
	A
06	12.2(.480)
08	14.7(.579)
10	17.3(.681)
12	19.8(.780)
14	22.3(.878)
16	24.9(.980)
20	30.0(1.181)
24	35.0(1.378)
26	37.6(1.480)
30	42.7(1.681)
34	47.7(1.878)
36	50.2(1.976)
40	55.4(2.181)
44	60.4(2.378)
50	68.1(2.681)
56	75.7(2.980)
60	80.8(3.181)
62	83.3(3.280)
64	85.8(3.378)

PART NUMBER:

101-XX-S

Number of circuits

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

**ON-SHORE TECHNOLOGY, INC.**

TITLE				101 Series Strain Relief- 2.54mm Dual Row IDC strain relief			
PART NO.		101-XX-S		DWG NO.		101-XX-S.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN			4050	
Steven 2007.08.27	Marvin 2007.08.27	Marvin 2007.08.27	Marvin 2007.08.27			Tolerance	
						UNIT: mm/inches	
				SHEET: 01/01		SCALE: NONE	
						X ±0.30/.012	
						XX ±0.20/.008	
						XXX ±0.10/.004	
						X* ±1°	