

Bridge Rectifiers

1.5 A Single Phase





Features :

- Ratings to 1,000 V PRV
- Surge overload rating - 30 / 50 amperes peak
- Ideal for printed circuit board
- Reliable construction utilizing moulded plastic
- Mounting position : Any

Mechanical Data:

Case	: Reliable low cost construction utilizing moulded plastic technique results in inexpensive product
Terminals	: Lead solderable per MIL-STD-202, Method 208
Polarity	: Polarity symbols marking on body



Dimensions : Inches (Millimetres)

Maximum Ratings and Electrical Characteristics:

Ratings at 25°C ambient temperature unless otherwise specified
Single phase, half wave, 60 Hz, Resistive or inductive load

For capacitive load, derate current by 20%		AM150	AM151	AM152	AM154	AM156	AM158	Unit
Maximum recurrent peak reverse voltage		50	100	200	400	600	800	V
Maximum RMS bridge input voltage		35	70	140	280	420	560	
Maximum DC blocking voltage		50	100	200	400	600	800	
Maximum average forward rectified current at T _A = 50°C	AM150	1.5						A
Peak forward surge current, 8.3 ms single half sinewave superimposed on rated load	AM150	50						
Maximum forward voltage drop per bridge element at 1 A dc		1						V
Maximum reverse current at rated T _A = 25°C		10						μA mA
DC blocking voltage per element T _A = 100°C		1						
I ² t rating for fusing (t <8.35 ms)		10						A ² S

Bridge Rectifiers

1.5 A Single Phase

For capacitive load, derate current by 20%	AM150	AM151	AM152	AM154	AM156	AM158	Unit
Typical junction capacitance per leg (Note 1) C _J	24						pF
Typical thermal resistance per leg (Note 2) R _{θJA}	36						°C / W
Typical thermal resistance per leg (Note 2) R _{θJL}	13						
Operating temperature range T _J	-55 to +125						°C
Storage temperature range T _A	-55 to +150						

Notes :

1 Measured at 1 MHz and applied reverse voltage of 4 volts

2 Thermal resistance from junction to ambient and from junction to lead mounted on PCB with 0.47 × 0.47 inches (12 × 12 mm) copper pads

Rating and Characteristic Curves

Figure 1 - Maximum Non-repetitive Surge Current




Figure 2 - Derating Curve for Output Rectified Current




Figure 3 - Typical Forward Characteristics (25°C)





Figure 4 - Typical Reverse Characteristics



Bridge Rectifiers



1.5 A Single Phase

Specification Table

V_{RRM} (V)	Maximum AC Input Voltage (V)	Current Rating (A)	I_{FSM} (A)	Body		Pin Spacing	Part Number
				Height	Diameter		
50	35	1.5	30	5.5	9.1	5.6	AM150
100	70						AM151
200	140						AM152
400	280						AM154
600	420						AM156
800	560						AM158

Order Multiple = 5

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.