

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

47362-1032

Status:

Active

Overview:

Serial ATA Host Receptacles

Description:

1.27mm Pitch Combo SATA Cable Connector, Straight Type, without Arris, with bumps, 0.38µm Gold (Au), 22 Circuits, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-47362-001 (PDF)

RoHS Certificate of Compliance (PDF)

General


Product Family	I/O Connectors
Series	47362
Application	Wire-to-Board
Comments	Straight Type
Component Type	Receptacle
Overview	Serial ATA Host Receptacles
Product Name	Serial ATA
Type	N/A
UPC	822350668866

Physical

Boot Color	N/A
Circuits (Loaded)	22
Circuits (maximum)	22
Circuits Detail	Signal 7, Power 15
Color - Resin	Black
Durability (mating cycles max)	50
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Number of Rows	1
Orientation	Straight
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.381µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Temperature Range - Operating	-35°C to +85°C
Termination Interface: Style	Solder or Weld
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	15V DC



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

47362Series

Material Info

Reference - Drawing Numbers

Product Specification	PS-47362-001
Sales Drawing	SD-47362-100

This document was generated on 11/06/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION