



83139 Double insulated 831392 Part number



IP 67 protection against hydrocarbons, detergents
Double break switching
Double insulated or Atex flameproof casing
Choice of actuators

Part numbers

	Type	Function	Connections
83139003	Standard 831390	I (changeover)	Standard lead output
MADE TO ORDER	Standard 831390	I (changeover)	Lead output on right/left
CONTACT US	Standard 831390	I (changeover)	Cable output
MADE TO ORDER	Low temperature 831395	I (changeover)	Standard lead output
MADE TO ORDER	Low temperature 831395	I (changeover)	Lead output on right/left
CONTACT US	Low temperature 831395	I (changeover)	Cable output
CONTACT US	Double insulated 831392	I (changeover)	Standard lead output
CONTACT US	Double insulated 831392	I (changeover)	Lead output on right/left
MADE TO ORDER	Double insulated 831392	I (changeover)	Cable output
MADE TO ORDER	Flameproof 831391	I (changeover)	Standard lead output
MADE TO ORDER	Flameproof 831391	I (changeover)	Lead output on right/left
CONTACT US	Flameproof 831391	I (changeover)	Cable output

Specifications

Electrical characteristics

Rating nominal / 250 V (A)	6
Rating thermal / 250 V (A)	11

Mechanical characteristics

Maximum operating force (N)	3
Min. Release force (N)	0,6
Maximum total travel force (N)	4
Max. permitted overtravel force (N)	10
Maximum rest position (mm)	B=9,8
Operating position depending on position of fixing holes (mm)	B = 8.7 ±0.4
Maximum differential travel (mm)	0,35 ±0,1
Min. overtravel (mm)	0,25
Ambient operating temperature (°C)	-20 → +85
Mechanical life (operations)	5 x 10 ⁶
Contact gap (mm)	0,3 x 2
Weight (g)	45

Fixations

Fixings - 4 holes (standard)	-
Fixing - 2 holes	B


Connections

Connection	Cable 3 x 0.75 mm ² length 0.50 m Ø ext. 5.2 mm
Standard wire output	-
Wire output on right	-

Additional specifications

- Components
- Material
- Case : polyester UL94V0
 - Contacts : silver
 - Membrane : nitrile for 83 139 0 silicon for 83 139 1/2/5
- Levers
- stainless steel
 - Roller : polyamide


Principles



Dimensions (mm)

Product

83 139 2
B fixing = 2 holes




N°	Legend
----	--------

①	R : 1.5 spherical
③	Cable 3 x 0.75 mm ² length 0.50 m 1 = black lead 2 = brown lead 3 = blue lead

Dimensions (mm)

Actuator mounting positions


Type 139
A fixing = 4 holes



Dimensions (mm)

Actuator mounting positions


Type 139
B fixing = 2 holes



Dimensions (mm)

Actuator mounting positions


Type 161
A fixing = 4 holes



Dimensions (mm)

Actuator mounting positions



Type 161
B fixing = 2 holes




Dimensions (mm)

Actuators


139 EX

**Dimensions (mm)****Actuators****139 AX****Dimensions (mm)****Actuators****161 A**

**Dimensions (mm)**


Actuators

161 E

**Dimensions (mm)**

Actuators


161 F



Dimensions (mm)


Actuators

161 G



Curves

Operating curve



N°	Legend
1	Number of cycles
2	Resistive circuit
3	Inductive circuit
4	Mechanical life limit
5	Current in Amps

Connections

Actuators and fixing positions

Part numbers for standard actuators		79 215 740	70 507 524	79 215 742	70 507 529
Actuators		Flat 139 AX R29.7 mm**	Roller 139 EX R28.7 mm**	Flat 161A R14.2 - R25.4 mm	Roller 161E R13.6 - R24.1 mm
Operating force - max.	N	1.5	1.5	2.6	1.7
Release force - min.	N	0.2	0.35	0.2	0.35
Differential travel	mm	1.5	0.7	1.25	0.7
Part numbers for standard actuators		70 507 528	79 218 651		
Actuators		Flat 161F R22.3 mm	Dummy roller 161 G R21.8		
Operating force - max.	N	2	2		
Release force - min.	N	0.2	0.2		
Differential travel	mm	1.1	1.1		

Unless indicated, flat actuators and roller actuators are delivered unmounted.
 ** Factory fitted

Note : We recommend greasing the switch pushbutton lightly when fitting actuators.

Other information

Product marking (83 139 1)

II 2 G

EEx d IIC T6

Unless otherwise specified, the characteristics given are applicable to all or part of the product range selected

Key to these symbols :

- Equipment used in potentially explosive atmospheres

II - Equipment group for surface use

2 - Equipment category for zone 1

G - Gas

EEx - The equipment complies with the protection methods standardised by CENELEC (European standards)

d - Protection method used : "d" flameproof casing

II - Surface industry

C - Most severe gas subdivision including hydrogen, acetylene and carbon disulphide

T6 - Temperature class corresponding to +85 °C

At the time of ordering, the customer must specify :

- The operating zone (0, 1 or 2)

- The type of atmosphere (gas or dust)

- The type of gas

- The ambient operating temperature

Product adaptations



- Special levers
- Special leads, cables, cable harnesses
- Specific operating temperatures

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crouzet:

[831392CBB.5.0](#) [831392CBB.5.A](#)