


### Fast Soft Recovery Rectifier Diode, 10 A



TO-220AC FULL-PAK



#### PRODUCT SUMMARY

$V_{RRM}$	200 to 600 V
$V_F$ at 10 A	< 1.2 V
$t_{rr}$	50 ns

#### FEATURES/DESCRIPTION

The 10ETF06FPPbF fast soft recovery rectifier series has been optimized for combined short reverse recovery time and low forward voltage drop.



RoHS\*  
COMPLIANT

The glass passivation ensures stable reliable operation in the most severe temperature and power cycling conditions.

The fully isolated package ( $V_{INS} = 2500$  V<sub>RMS</sub>) is UL E78996 approved.

This product series has been designed and qualified for industrial level and lead (Pb)-free.

#### APPLICATIONS

- Output rectification and freewheeling in inverters, choppers and converters
- Input rectifications where severe restrictions on conducted EMI should be met

#### MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
$V_{RRM}$		200 to 600	V
$I_{F(AV)}$	Sinusoidal waveform	10	A
$I_{FSM}$		150	
$t_{rr}$	1 A, 100 A/μs	50	ns
$V_F$	10 A, $T_J = 25$ °C	1.2	V
$T_J$		- 40 to 150	°C

#### VOLTAGE RATINGS

PART NUMBER	$V_{RRM}$ , MAXIMUM PEAK REVERSE VOLTAGE V	$V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	$I_{RRM}$ AT 150 °C mA
10ETF02FPPbF	200	300	2
10ETF04FPPbF	400	500	
10ETF06FPPbF	600	700	

#### ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum average forward current	$I_{F(AV)}$	$T_C = 98$ °C, 180° conduction half sine wave	10	A
Maximum peak one cycle non-repetitive surge current	$I_{FSM}$	10 ms sine pulse, rated $V_{RRM}$ applied	150	
Maximum $I^2t$ for fusing	$I^2t$	10 ms sine pulse, no voltage reapplied	160	$A^2s$
		10 ms sine pulse, rated $V_{RRM}$ applied	112.5	
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	$t = 0.1$ to 10 ms, no voltage reapplied	1600	$A^2\sqrt{s}$

\* Pb containing terminations are not RoHS compliant, exemptions may apply

# 10ETF..FPPbF Soft Recovery Series

Vishay High Power Products

Fast Soft Recovery  
Rectifier Diode, 10 A



## ELECTRICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum forward voltage drop	$V_{FM}$	10 A, $T_J = 25^\circ C$		1.2	V
Forward slope resistance	$r_t$	$T_J = 150^\circ C$		23.5	$m\Omega$
Threshold voltage	$V_{F(TO)}$			0.85	V
Maximum reverse leakage current	$I_{RM}$	$T_J = 25^\circ C$	$V_R = \text{Rated } V_{RRM}$	0.1	mA
		$T_J = 150^\circ C$		3.0	

## RECOVERY CHARACTERISTICS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Reverse recovery time	$t_{rr}$	$I_F$ at 10 A $p$ $25 A/\mu s$ $25^\circ C$	145	ns	
Reverse recovery current	$I_{rr}$		2.75	A	
Reverse recovery charge	$Q_{rr}$		0.32	$\mu C$	
Snap factor	S		0.6		

## THERMAL - MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	$T_J, T_{Stg}$		- 40 to 150	$^\circ C$
Maximum thermal resistance junction to case	$R_{thJC}$	DC operation	2.5	$^\circ C/W$
Maximum thermal resistance junction to ambient	$R_{thJA}$		62	
Typical thermal resistance, case to heatsink	$R_{thCS}$		0.5	
Approximate weight			2	g
			0.07	oz.
Mounting torque	minimum		6 (5)	$kgf \cdot cm$ (lbf · in)
	maximum		12 (10)	
Marking device		Case style TO-220AC FULL-PAK (94/V0)	10ETF06FP	




Fig. 1 - Current Rating Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - Forward Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current

# 10ETF..FPPbF Soft Recovery Series

Vishay High Power Products

Fast Soft Recovery  
Rectifier Diode, 10 A




Fig. 7 - Forward Voltage Drop Characteristics




Fig. 10 - Recovery Charge Characteristics,  $T_J = 25\text{ }^{\circ}\text{C}$




Fig. 8 - Recovery Time Characteristics,  $T_J = 25\text{ }^{\circ}\text{C}$




Fig. 11 - Recovery Charge Characteristics,  $T_J = 150\text{ }^{\circ}\text{C}$




Fig. 9 - Recovery Time Characteristics,  $T_J = 150\text{ }^{\circ}\text{C}$




Fig. 12 - Recovery Current Characteristics,  $T_J = 25\text{ }^{\circ}\text{C}$




Fig. 13 - Recovery Current Characteristics,  $T_J = 150^\circ\text{C}$




Fig. 14 - Thermal Impedance  $Z_{thJC}$  Characteristics

# 10ETF..FPPbF Soft Recovery Series

Vishay High Power Products

Fast Soft Recovery  
Rectifier Diode, 10 A



## ORDERING INFORMATION TABLE

Device code	10	E	T	F	06	FP	PbF
	1	2	3	4	5	6	7

- 1** - Current rating (10 = 10 A)
- 2** - Circuit configuration:  
E = Single diode
- 3** - Package:  
T = TO-220AC
- 4** - Type of silicon:  
F = Fast soft recovery rectifier
- 5** - Voltage code x 100 =  $V_{RRM}$  →
  - 02 = 200 V
  - 04 = 400 V
  - 06 = 600 V
- 6** - FULL-PAK
- 7** - • None = Standard production  
• PbF = Lead (Pb)-free

LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95005">http://www.vishay.com/doc?95005</a>
Part marking information	<a href="http://www.vishay.com/doc?95009">http://www.vishay.com/doc?95009</a>

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.