



Main

Commercial Status	Commercialised
Range of product	Zelio Logic
Product or component type	GSM modem
Type of modem	Type quad band 900/1800 MHz, 850/1900 MHz
Data backed up	Flash memory

Complementary

Kit composition	1 antenna with cable 1 supply cable 2 lugs for plate mounting Fixing on DIN rail (assembled with the GSM modem) GSM modem
Function available	Send alarm/receive instruction Send alarm to e-mail address Transfer program Update firmware monitoring
Number of messages	<= 28
Electrical data recording	Date and time Discrete and digital value Telephone/E-mail
[Us] rated supply voltage	12...24 V DC
Supply voltage limits	5.5...32 V
Supply current	87 A 24 V 165 mA 12 V <= 2100 mA 5.5 V
Power dissipation in W	2.1 W
Associated fuse rating	2.5 A
Electrical connection	Supply cable 1 cable Com-Z Com-Z specific to Zelio, specific Zelio communication protocol for Zelio Logic smart relays SR.B..... and SR2 E..... Version (>= V3.1) 1 cable Com-M Com-M specific to Zelio RS232 serial, specific Zelio communication protocol for link with the modem, AT commands 1 cable 1 antenna with cable
Cable length	2.5 m antenna with cable 1.5 m supply cable
Insulation	By the cable SR2 CBL07, connector type: Com-M specific to Zelio 1780 V optocoupler, connector type: Com-Z specific to Zelio
Connections - terminals	Screw terminals, 2 x 0.25...2 x 0.75 mm ² , 24...18, flexible cable with cable end Screw terminals, 1 x 0.25...1 x 2.5 mm ² , 24...14, flexible cable with cable end Screw terminals, 2 x 0.25...2 x 1.5 mm ² , 23...16, solid cable Screw terminals, 1 x 0.25...1 x 2.5 mm ² , 24...14, solid cable Screw terminals, 1 x 0.25...1 x 2.5 mm ² , 24...14, semi-solid cable
Tightening torque	0.5 N.m
Product weight	0.335 kg

Environment

Product certifications	CSA C-Tick FCC part 15 standard GOST IC PTCRB UL
Standards	EN/IEC 60068-2-32 EN/IEC 60068-2-6 Fc
IP degree of protection	IP31 conforming to IEC 60529
Environmental characteristic	R and TTE directive conforming to ETSI EN 301511 R and TTE directive conforming to ETSI EN 301489-7 R and TTE directive conforming to ETSI EN 301419-1 Low voltage directive conforming to EN/IEC 60950-1 EMC directive conforming to EN 301489-1
Disturbance radiated/conducted	Class B conforming to EN 55022-11 group 1
Pollution degree	2 conforming to EN/IEC 61131-2
Ambient air temperature for operation	-20...55 °C conforming to IEC 60068-2-1 and IEC 60068-2-2
Ambient air temperature for storage	-40...70 °C
Operating altitude	2000 m
Altitude transport	<= 3048 m
Relative humidity	95 % without condensation during storage 95 % at 55 °C without condensation

RoHS compliance


RoHS EUR status	Compliant
RoHS EUR conformity date(YYWW)	0626

Contractual warranty


Period	18 months
--------	-----------

GSM Modem

Rail Mounting



Screw Fixing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SR2MOD02](#)