


Art.- No.	Bemessungswerte/Ratings/Valeurs assignées Strom Current Courant	Spannung Voltage Tension	Ausschaltvermögen Breaking capacity Pouvoir de coupure	Spannungsfall Voltage drop Chute de tension max [mV]	Verlustleistung Sustained dissip. Valeur de dissip. max.[W]	Schmelzintegral Melting integral Intégral de fusion [A ² s]
632.602 ¹⁾ 632.603 ¹⁾	32 mA 40 mA	250 V	35 A	auf Anfrage /	on request /	à demande
632.604	50 mA			10.000	1,6	0,00125
632.605	63 mA			8.000		0,00167
632.606	80 mA			7.000		0,00128
632.607	100 mA			6.000		0,00200
632.608	125 mA			5.500		0,00469
632.609	160 mA			5.000		0,00870
632.610	200 mA			4.000		0,02000
632.611	250 mA			3.500		0,03250
632.612	315 mA			3.000		0,06747
632.613	400 mA			2.500		0,15
632.614	500 mA			2.000		0,28
632.615	630 mA			1.800		0,47
632.616	800 mA			1.500		0,54
632.617	1 A			500		0,52
632.618	1,25 A			400	2,5	2,66
632.619	1,6 A			400		5,32
632.620	2 A			300		9,52
632.621	2,5 A			250		19,75
632.622	3,15 A	150 V	40 A	250	4	25,60
632.623	4 A	150 V		250		51,20
632.624	5 A	60 V		200		65,50
632.625	6,3 A	60 V		200		103,99
632.626	8 A	60 V		200		206,08
632.627	10 A	60 V		200		260,00
632.628 ¹⁾ 632.630 ¹⁾	12,5 A 16 A	60 V 60 V	100 A	auf Anfrage /	on request /	à demande

Aufbau: Glasrohr, durchsichtig
Kontaktkappen: Messing, vernickelt
Verpackung: 100 St. = 10 x 10 Faltschachteln
500 St. = Industrieverpackung

Construction: Glasstube, transparent
Contact caps: Brass, nickel plated
Packing: 100 pcs. = 10 boxes of 10 pieces
500 pcs. = Industrial boxes

Construction: Tube verre, transparent
Cabochons de contact: Laiton, nickelé
Emballage: 100 pcs. = en 10 boîtes de 10 pièces
500 pcs. = en emballage industriel

Strom-Zeit-Kennlinien
Current Time Characteristics
Caractéristique courant/temps



Schmelzzeit-Grenzwerte / Pre-arcing time limits / Temps de fusion limité

Bemessungsstrom Rated current Courant assigné	2,0 I _{rat} max.	2,75 I _{rat} min. max.	4 I _{rat} min. max.	10 I _{rat} max.
50 - 100 mA	20 s	2 ms 200 ms	1 ms 30 ms	5 ms
125 mA - 10 A	20 s	20 ms 1.500 ms	8 ms 400 ms	80 ms

1) Nicht in der Normenreihe verzeichnet / Not mentioned in the standards / Pas mentionné dans la norme.