

Technical drawing of a shaft with the following dimensions and features:

- Overall length:  $.477 \text{ REF}$  [ $12.12$ ]
- Distance from left end to start of cross-hatched section:  $.165 \pm .016$  [ $4.19 \pm 0.41$ ]
- Distance from left end to end of cross-hatched section:  $.312 \pm .016$  [ $7.92 \pm 0.41$ ]
- Length of cross-hatched section:  $.219 \pm .016$  [ $5.56 \pm 0.41$ ]
- Surface texture symbol:  $\triangle 6$

R  
PER


FERRULE  
MATERIAL: COPPER PER  
ASTM-B-152.  
FINISH: GOLD PLATE PER  
MIL-G-45204

- PART NO.

TE Connectivity

CONNECTOR, COAXIAL, RF  
SOCKET SIZE 5, ARINC  
(HEX CRIMP)

|      |           |            |               |        |     |
|------|-----------|------------|---------------|--------|-----|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |        |     |
| A2   | 00779     | C-225791-9 | —             |        |     |
|      |           |            | SCALE         | SHEET  | REV |
|      |           |            | 5:1           | 1 OF 1 | D   |

|                                                                                       |                                            |                                                                                                         |                  |
|---------------------------------------------------------------------------------------|--------------------------------------------|---------------------------------------------------------------------------------------------------------|------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                            | DWN<br>C.C.THOMAS<br>CHK<br>J.DUNBAR<br>APVD<br>—<br>PRODUCT SPEC<br>108-12045<br>APPLICATION SPEC<br>— | 2-1-95<br>2-2-95 |
| DIMENSIONS:<br><br>INCHES                                                             | TOLERANCES, UNLESS<br>OTHERWISE SPECIFIED: |                                                                                                         |                  |
|  | 0 PLC ± —                                  |                                                                                                         |                  |
|                                                                                       | 1 PLC ± —                                  |                                                                                                         |                  |
|                                                                                       | 2 PLC ± —                                  |                                                                                                         |                  |
|                                                                                       | 3 PLC ± —                                  |                                                                                                         |                  |
|                                                                                       | 4 PLC ± —                                  |                                                                                                         |                  |
| ANGLES                                                                                | ± —                                        |                                                                                                         |                  |
| MATERIAL                                                                              | FINISH                                     | WEIGHT                                                                                                  | —                |
| SEE CALLOUTS                                                                          | SEE CALLOUTS                               | CUSTOMER DRAWING                                                                                        |                  |