



## Dimensions: mm (In.)

**Electrical Specifications:**

- 3A/125VAC, 1A/250VAC
- Insulation Resistance: 500VDC 100MΩ(min)
- Dielectric Strength: 1500VAC 1 minute
- Contact Resistance: 2.5VDC 1A 20mΩ(max)

**Materials:**

- Lead is silver clad-copper (AG + CU) and is finished BL silver-plating.
- Moveable contact arm is silver clad copper (AG + CU)

Mouser Stock No.	Button Type	Button Color or Treatment	Frame Color or Treatment	Circuit
10PA348	Rectangular	Notching	Black Mould	Off-(On)
10PA349	Rectangular	Notching	Metal Plated	Off-(On)

**Pushbutton Switches**

10PA348, 10PA349

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10PA348](#) [10PA349](#)