




FB-EM-30348-000

SHT 1.1



TOP VIEW
W/WINDSHIELD SHOWN
SCALE 1:1



WIRE COLOR			WEIGHT GRAMS
+ve	OUTPUT	-ve	
RED	WHITE	BLACK	---

DIMENSIONS IN MILLIMETERS [INCHES]

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
C	C40100518	11-25-10		
B	C10107748	8-12-08		
A	C10107379	6-26-08	Active	C


KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

SCALE:	1:1	DR. BY	DATE
	DO NOT SCALE DRAWING	TT	6-26-08
TITLE:	BOOM MICROPHONE	CK. BY	DATE
	FB-EM-30348-000	GJP	7-15-08
	OUTLINE DRAWING	APP. BY	DATE
		GJP	7-15-08

SHT 1.1

KELIASIZE.FRM


Rev. B



FREQUENCY	SENSITIVITY			DEVICE CONFORMITY RANGE OF DEVIATION FROM 1KHz
	MIN.	NOM.	MAX.	
300	---	-48.0	---	-3.0 +3.0
1000	-51.0	-48.0	-45.0	0.0 0.0
4000	---	-47.0	---	-3.0 +5.0

NOTES:

1. MICROPHONE TO BE FUNCTIONAL WITH 10 VDC SUPPLY.
2. SENSITIVITY VALUES INDICATED ON THIS SPECIFICATION ARE VALID AT 50% HUMIDITY.
3. TEST CONDITIONS:
HEAD OF BOOM EXPOSED TO 74 dB SPL SWEPT SOUND FIELD AT 6mm FROM VOICE APERTURE.
ARTIFICIAL VOICE:
B & K 4227 MOUTH SIMULATOR.
4. FOR MICROPHONE CAPSULE SPEC. SEE DRAWING EK-23132-C36 SHEET 2.1.
5. SURVIVES 10m SUBMERSION BASED ON QUALIFICATION TESTING. 100% TEST 30 MINUTES IN SUBMERSION; SENSITIVITY WITHIN 3dB OF INITIAL SENSITIVITY AFTER DRIED FOR 30 MINUTES AT ROOM TEMPERATURE.

LEAD IDENTIFICATION
& TEST CIRCUIT

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
C	C40100518	11-25-10	Active	C
B	C10107748	8-12-08		
A	C10107379	6-26-08		

WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION

DR. BY	DATE
TT	6-26-08
CK. BY	DATE
GJP	7-15-08
APP. BY	DATE
GJP	7-15-08

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.TITLE: BOOM MICROPHONE FB-EM-30348-000
PERFORMANCE SPECIFICATION SHT 2.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[FB-EM-30348-000](#)