

PROGRAMMABLE OSCILLATORS (SMD • Ceramic Package)

RoHS compliant

CSX-750P SERIES


2000pcs/reel




FEATURES

- Wide range of output frequency by PLL technology.
- Quick sample delivery and short lead time in mass production.
- Low current consumption with output enable function (OE) or stand by function (STAND-BY).
- Suitable for various applications such as communication devices, AV devices and measuring instruments.

DIMENSION [mm]



SOLDER PAD LAYOUT [mm]



STANDARD SPECIFICATIONS * Model is determined by the selection for the output enable or stand-by function, the frequency stability and the supply voltage.

Item	Model	OE	CSX-750 PT (＊)	CSX-750 PC (＊)	CSX-750 PB (＊)
		STAND-BY	CSX-750 PK (＊)	CSX-750 PD (＊)	CSX-750 PJ (＊)
Frequency Range			1.000MHz ～ 125.000MHz		1.000MHz～100.000MHz
Supply Voltage			Vdd : 5.0V±0.5V		Vdd : 3.3V±0.3V
Frequency Stability (＊)			B : ±50ppm, C : ±100ppm, E : ±50ppm (－40℃～＋85℃), F : ±100ppm (－40℃～＋85℃)		
Operating Temperature Range			－20℃～＋70℃ (－40℃～＋85℃)		
Storage Temperature Range			－55℃～＋125℃		
Current consumption			45mA Max.		25mA Max.
Duty	TTL level (1.4V)		45～55%	－	
	CMOS level (1/2 Vdd)		－	45～55%	
Output Voltage	V _{OH}		0.9Vdd Min.		
	V _{OL}		0.4V Max.		0.1Vdd Max.
Output Load	TTL		5TTL Max.	－	
	CMOS		－	25pF Max.	15pF Max.
Rise and Fall Time			4 nsec Max.		
Start-up time			10 msec Max.		
Input Voltage	V _{IH}		2.0V Min.		0.7Vdd Min.
	V _{IL}		0.8V Max.		0.2Vdd Max.
Disable current			30mA Max.		15mA Max.
Stand-by current			50 μA Max.		20 μA Max.