





- 1 HOUSING: PBT, UL94V-0, COLOR: BLUE.
POSTS: PHOSPHOR BRONZE.
LATCHES: ZINC ALLOY.
- 2 POSTS: GOLD FLASH OVER
PALLADIUM-NICKEL PLATE, 0.76µm[.000030] MIN TOTAL ON MATING AREA,
2.54µm[.000100] MIN TIN PLATE ON THE SOLDER-TAIL, ALL OVER
1.27µm[.000050] MIN NICKEL UNDERPLATE ON ENTIRE POST.
OR
0.76µm[.000030] MIN GOLD PLATE ON MATING AREA,
2.54µm[.000100] MIN TIN PLATE ON THE SOLDER-TAIL, ALL OVER
1.27µm[.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
LATCHES: BLACK NICKEL OVER COPPER.
- 3 DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.
- 4 ALTERNATE LOCATION/ORIENTATION FOR POSITION #1 INDICATOR.



40.64 [1.600]	16	42.67 [1.680]	48.16 [1.896]	50.80 [2.000]	34	3-1761721-1
E	D	C	B	A	NO OF POS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		0 PLC ± -		DWN B MCMMASTER 07SEP05		
		1 PLC ± -		CHK S.BOLASH 07SEP05		
		2 PLC ± -		APVD M.WALMSLEY 07SEP05		
		3 PLC ± 0.13[.005]		NAME		
4 PLC ± -		ANGLES ± -		PRODUCT SPEC		
MATERIAL		FINISH		APPLICATION SPEC		
1		2		SIZE CAGE CODE DRAWING NO		
				RESTRICTED TO		
				A1 00779 C=1761721		
				CUSTOMER DRAWING		
				SCALE 4:1 SHEET 1 OF 1 REV D		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1761721-1](#)