samtec

E.L.P.™
EXTENDED LIFE PRODUCT
10 year Mixed Flowing Gas with 30µ" Gold
Call Samtec for maximum mated cycles



(1,27 mm) .050"

CLP SERIES

LOW PROFILE DUAL WIPE SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLP

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Sn or Au over
50µ" (1,27 µm) Ni
Current Rating (CLP/FTSH):
3.3 A per pin
(1 pin powered per row)
Voltage Rating:
240 VAC/340 VDC
Operating Temp Range:
-55°C to +125°C
Contact Resistance:
10 mΩ
Insertion Depth:
Top Entry = (1,40 mm) .055" minimum, Bottom Entry = (2,41 mm) .095" minimum plus board thickness
DH Entry = (2,31 mm) .091" to (2,67 mm) .105"
Insertion Force:
(Single contact only)
3.8 oz (1,05 N) average
Normal Force:
60 grams (0,59 N) average
Withdrawal Force:
(Single contact only)
2 oz (0,56 N) average
Max Cycles:
100 with 10µ" (0,25 µm) Au
RoHS Compliant:
Yes

Processing:

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0,10 mm) .004" max (02-35)
(0,15 mm) .006" max (36-50)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594

ALSO AVAILABLE
(MOQ Required)

- Single row
- Other platings

Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.

Mates with:
FTSH, FTS, FW





CLP	–	1	NO. PINS PER ROW	–	02	–	PLATING OPTION	–	ROW OPTION	–	OTHER OPTION

02 thru 50

–F
= Gold flash on contact, Matte Tin on tail

–L
= 10µ" (0,25 µm) Gold on contact, Matte Tin on tail

–G
= 10µ" (0,25 µm) Gold (–D only)

–D
= Double Row

–DH
= Double Horizontal (Requires FTSH –01 lead style)

–BE
= Bottom Entry (Required for bottom entry applications)

–A
= Alignment Pin (Not available with –PA option) (05, 06, 07, 08, 10, 12, 15, 20, 25, 30, 40 positions only) (–DH option and other sizes. Contact Samtec.)

–K
= (4,00 mm) .157" DIA Polyimide film Pick & Place Pad (5 positions min.)

–P
= Pick & Place Pad (5 positions min. –D only) (Not always necessary for auto placement. See Flex Processing.)

–PA
= Pick & Place Pad with Alignment Pin (–D only) (Not Available with –A option)

–TR
= Tape & Reel







PIN/ROW	A
04-15	(3,56) .140
16-50	(7,11) .280



If odd pins/row, alignment pins are on middle position on centerline of the part. If even pins/row, then alignment pins are between middle two positions.

Due to technical progress, all designs, specifications and components are subject to change without notice.