

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300300070

Status:


Active

Overview:

Brad Nano-Change (M8) Products

Description:

Mini-Change to Nano-Change (M8) Double-Ended Cordset, 5 Poles, Female (90°) to Male (90°), 26 AWG, PVC Cable, 1.0m (3.28') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	130030
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Region	Europe
Type	Double Ended
UPC	78678882278
Physical	
Cable Diameter	N/A
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to 90°
Poles	5
Temperature Range - Operating	-20°C to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded-Twisted Pair
Electrical	
Current - Maximum per Contact	1.68A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	845033D12M010
Reference - Drawing Numbers	
Sales Drawing	SD-130030-070

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130030 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION