


4 mm Square SMD Light Touch Switches

Type: **EVQP6/EVQ6P6/EVQ7P6/EVQ9P6**



■ Features

- External dimensions : 4.1 mm×4.1 mm
Height :Without Push Plate 0.35 mm, With Push Plate 0.58 mm
:Without Push Plate-With Ground Terminal 0.43 mm
- Long-life :1000000 cycles min.
(Operating Force 1.6 N Type)
- Dust-proof structure

■ Recommended Applications

- Operating switches for portable electronic equipment
(Mobile phones, Camcorders, Portable audio players, etc.).

■ Explanation of Part Numbers

1	2	3	4	5	6	7	8	9
E	V	Q						
Product Code						Height		
			Type					
			P6□			· With Push Plate, Without Push Plate · Without Ground Terminal		
			6P6 7P6 9P6			· Without Push Plate · With Ground Terminal		

■ Product Chart

Height	Without Push Plate H=0.35 mm	With Push Plate H=0.58 mm	Without Push Plate With Ground Terminal H=0.43 mm
Packaging	Embossed	Embossed	Embossed
Operating Force			
1.0 N	—	—	EVQ7P6
1.6 N	EVQP6D	EVQP6L	EVQ6P6
2.4 N	EVQP6P	EVQP6Y	EVQ9P6

■ Specifications













Type		Snap action / Push-on type SPST	
		Without Push Plate	With Push Plate
Electrical	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	500 m Ω max.	
	Insulation Resistance	50 M Ω min.	
	Dielectric Withstanding Voltage	100 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 10 ms max. (OFF)	
Mechanical	Operating Force	1.0 N, 1.6 N, 2.4 N	
	Travel	0.2 mm (EVQ7P6 : 0.15 mm)	
Endurance	Operating Life	1.0 N, 1.6 N : 1000000 cycles min. 2.4 N : 500000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		10000 pcs. Embossed Taping (Reel Pack)	
Quantity/Cartron		50000 pcs.	

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.







00 Oct. 2012

■ Dimensions in mm (not to scale)


<div>No. 1</div> <div>EVQP6D EVQP6P</div> <div>(Embossed Taping)</div> <div>Surface mount For reflow soldering Without push plate</div> <div></div>		<div></div> <div>Marking*</div> <div></div> <div>Circuit diagram</div> <div></div> <div>PWB land pattern for reference</div> <div>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</div> <div>*Marking varies according to push force.</div>		
<div>Part Numbers</div> <div>EVQP6DB35</div> <div>EVQP6PB35</div>		<div>Operating Force</div> <div>1.6 N</div> <div>2.4 N</div>	<div>Height</div> <div>0.35 mm</div> <div>0.35 mm</div>	<div>Operating Life</div> <div>1000000 cycles</div> <div>500000 cycles</div>
<div>No. 2</div> <div>EVQP6L EVQP6Y</div> <div>(Embossed Taping)</div> <div>Surface mount For reflow soldering With push plate</div> <div></div>		<div></div> <div></div> <div>Circuit diagram</div> <div></div> <div>PWB land pattern for reference</div> <div>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</div>		
<div>Part Numbers</div> <div>EVQP6LB55</div> <div>EVQP6YB55</div>		<div>Operating Force</div> <div>1.6 N</div> <div>2.4 N</div>	<div>Height</div> <div>0.58 mm</div> <div>0.58 mm</div>	<div>Operating Life</div> <div>1000000 cycles</div> <div>500000 cycles</div>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

<p>No. 3</p> <p>EVQ7P6 EVQ6P6 EVQ9P6</p> <p>(Embossed Taping)</p> <p>Surface mount For reflow soldering Without push plate With Ground Terminal</p> 	 <p>Operation point</p> <p>(5-φ0.4)</p> <p>(4.3) 4.1±0.2 (0.5) 4.1±0.2 0.6 2.9 A B A' B' φ2.6 0.25 0.38±0.15 (3.7) (2.4) (1.4) (1.5) (1.4) (1.5) (0.85) (1.6) (1.9) (1.4)</p> <p>0.43</p> <p>Circuit diagram</p>  <p>PWB land pattern for reference</p>  <p>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</p>		
Part Numbers	Operating Force	Height	Operating Life
EVQ7P6B40	1.0 N	0.43 mm	1000000 cycles
EVQ6P6B40	1.6 N	0.43 mm	1000000 cycles
EVQ9P6B40	2.4 N	0.43 mm	500000 cycles

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia.	t ₁	t ₂
EVQP6	0.35/0.58	4.0±0.2	5.0±0.2	12.0 ^{+0.3} _{-0.1}	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₀	0.30±0.05	0.5/0.7 ^{+0.2} _{-0.1}
EVQ6P6	0.43											
EVQ7P6												
EVQ9P6												


● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.5	17.5±1.0	1.0 to 3.0	1.0±0.5

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EVQ-P6DB35](#) [EVQ-P6JE35](#) [EVQ-P6LB55](#) [EVQ-P6PB35](#) [EVQ-P6YB55](#) [EVQ-6P6B40](#) [EVQ-9P6B40](#) [EVQ-7P6B40](#)