








PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: NYLON 6T
FLAMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: TIN
QUALITY CLASS: 25 MATING CYCLES
PITCH: 3.00MM

ENVIRONMENTAL
OPERATING TEMPERATURE: -25 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 5A
WORKING VOLTAGE: 250V AC
INSULATOR RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN
CONTACT RESISTANCE: 10 MOHM MAX


STANDARD
CERTIFIED: E323964 / MODEL NUMBER 662-R

SOLDERING
REFLOW PROCESS ONLY

PACKAGING
TRAY

DIMENSION
A = 3.00 x (NB. PIN / 2 - 1)
B = 3.00 x (NB. PIN / 2 + 1) + 0.70

NB. PIN	C	NB. PIN	C
2 to 6	-	16	16.68
8	4.68	18	19.68
10	7.68	20	22.68
12	10.68	22	25.68
14	13.68	24	28.68

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			
G								
F	20-DEC-11	LAYOUT	GG					
E	05-AUG-11	C DIMENSION	QL					
D	10-OCT-10	DIAMETER	GG					
C	18-NOV-09	STANDARD	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: 3.00MM MALE DUAL ROW SMT RIGHT ANGLE HEADER WITH PLASTIC PEGS	SIZE A4	
B	03-AUG-09	DIMENSION C	JP		SCALE:			
A	27-JUL-09	REAR PIN	JP		SHEET: 1/1			WERI PART NO: 662 0xx 236 022
REV	DATE	FILE	BY		DRAW: JACK			