



Series 800 Mighty Mouse, UN Mating Thread PC Tail or Solder Cup, Hermetic Receptacle

800-013 How to Order



Compact, Rugged Series 800 hermetic receptacles feature 304L stainless steel shells and vitreous glass insulators. Contacts are gold-plated iron alloy. UN mating thread. Available with male pin contacts (contact Glenair for hermetic connectors with female socket contacts). 100% helium leak tested to meet 1×10^{-7} cc/second maximum leak rate. Contacts are factory-installed and are non-removable. Terminate to wires with solder cup versions, or choose PC tail versions for thru-hole soldering to rigid or flexible circuit boards. Available in all contact and insert arrangements between size 5 and 12.

How To Order

Sample Part Number

800-013

-02

Z1

6-7

P

N

Series 800-013 Hermetic Receptacle

Shell Style (See Table I) 02 = Square Flange 03 = Solder Mount 07 = Jam-Nut

Shell Material and Finish Z1 = Stainless Steel / Passivated RoHS Compliant
ZL = Stainless Steel / Nickel Plated

Shell Size - Insert Arrangement See Contact Arrangements page C-2

Contact Type P = Pin, Solder Cup S = Socket, Solder Cup C = Pin, PC Tail D = Socket, PC Tail

Shell Keyway Position N = Normal X = Pos. X Y = Pos. Y Z = Pos. Z

Table I: Shell Style

-02 Square Flange	-03 Solder Mount	-07 Jam-Nut


Table II: Contact Dimensions

Contact Size	Ø EE
23	.022/.018
20	.028/.024
16	.064/.060
12	.096/.092

Table III: CC and DD Dia.

Shell Size	Ø CC O.D.	Ø DD O.D.
5	.290 (7.37)	.197 (5.00)
6	.330 (8.38)	.256 (6.50)
7	.380 (9.65)	.325 (8.25)
8	.450 (11.43)	.390 (9.91)
9	.500 (12.70)	.452 (11.48)
10	.575 (14.60)	.520 (13.21)
12	.660 (16.76)	.610 (15.49)

Solder mount receptacle - shell style 03 - shell size 5 and 6



* See Table II
** See Table III



Dimensions in Inches (millimeters) are subject to change without notice.

**Series 800 Mighty Mouse, UN Mating Thread
PC Tail or Solder Cup, Hermetic Receptacle
800-013 Shell Size 5 and 6 Dimensions**





Series 800

Square flange mount receptacle - shell style 02 - shell size 5 and 6



Jam nut mount receptacle - shell style 07 - shell size 5 and 6



Solder Mount Dimensions		
Shell Size	Ø M	N Thread
5	.400 (10.16)	.3125-28 UN-2A
6	.455 (11.56)	.3750-28 UN-2A

Square Flange Dimension					
Shell Size	Ø G	Ø H	J Sq	K BSC	L Thread
5	.096 (2.44)	.680 (17.27)	.527 (13.39)	.363 (9.22)	.3125-28 UN-2A
6	.091 (2.31)	.750 (19.05)	.588 (14.94)	.423 (10.74)	.3750-28 UN-2A

Jam-Nut Dimensions				
Shell Size	Ø A	B Flat	C Flat	D Thread
5	.541 (13.74)	.500 (12.70)	.285 (7.24)	.3125-28 UN-2A
6	.610 (15.49)	.562 (14.27)	.352 (8.94)	.3750-28 UN-2A

Master Key Positions, Shell Size 5-6		
Position		
N	150°	
X	140°	
Y	130°	
Z	120°	

Jam-Nut Panel Cut Out		
Shell Size	Ø A	B Flat
5	.322 (8.18)	.299 (7.59)
	.317 (8.05)	.295 (7.49)
6	.385 (9.78)	.362 (9.19)
	.380 (9.65)	.358 (9.09)

Material / finish:

- Shell: CRES / see How to Order Table
- Jam-nut: CRES 303; see How to Order Table
- Contact: alloy 52 gold plate
- Socket: fluorosilicone / N.A.
- Seals: fluorosilicone / N.A.
- Insulator, hermetic: glass / N.A.
- Insulator, socket: high-grade dielectric / N.A.

Dimensions in Inches (millimeters) are subject to change without notice.


**Series 800 Mighty Mouse, UN Mating Thread
PC Tail or Solder Cup, Hermetic Receptacle
800-013 Shell Size 7 thru 12 Dimensions**

Solder mount, front panel mount receptacle - shell style 03 - shell size 7 thru 12

Master Key Positions, Shell Size 7-12

Position	
N	150°
X	140°
Y	130°
Z	120°

Square Flange Mount Dimensions		
Shell Size	Ø A	B Thread
7	.520 (13.21)	.4375-28 UNEF-2A
8	.650 (16.51)	.5000-32 UN-2A
9	.764 (19.41)	.5625-32 UN-2A
10	.775 (19.68)	.6250-32 UN-2A
12	.858 (21.79)	.7500-28 UN-2A



Material / finish:

- Shell: CRES / see How to Order Table
- Contacts: alloy 52 / gold plate
- Sockets: copper alloy / gold plate
- Seals: fluorosilicone / N.A.
- Insulator, hermetic: fused glass / N.A.
- Insulator, socket: high-grade dielectric / N.A.


* See Table II

** See Table III

Square flange, front panel mount receptacle - shell style 02 - shell size 7 thru 12

Master Key Positions, Shell Size 7-12

Position	
N	150°
X	140°
Y	130°
Z	120°



* See Table II

** See Table III

Solder Mount Dimensions					
Shell Size	Ø A	Ø B	C SQ	D BSC	E Thread
7	.096 (2.44)	.830 (21.08)	.650 (16.51)	.483 (12.27)	.4375-28 UNEF-2A
8	.091 (2.31)	.935 (23.75)	.710 (18.03)	.542 (13.77)	.5000-32 UN-2A
9	.130 (3.30) .126 (3.20)	1.250 (31.75)	.938 (23.83)	.719 (18.26)	.5625-32 UN-2A
10		1.250 (31.75)	.938 (23.83)	.719 (18.26)	.6250-32 UN-2A
12		1.375 (34.92)	1.031 (26.19)	.812 (20.62)	.7500-28 UN-2A

Material / finish:

- Shell: CRES / see How to Order Table
- Contacts: alloy 52 / gold plate
- Socket: copper alloy / gold plate
- Seals: fluorosilicone / N.A.
- Insulator, hermetic: fused glass / N.A.
- Insulator, socket: high-grade dielectric / N.A.


Dimensions in Inches (millimeters) are subject to change without notice.

**Series 800 Mighty Mouse, UN Mating Thread
PC Tail or Solder Cup, Hermetic Receptacle**
800-013 Shell Size 7 thru 12 Dimensions



Series 800

Jam-nut, rear panel mount receptacle - shell style 07 - shell size 7 thru 12



* See Table II
** See Table III

C

Keyway Positions, Shell Size 7-12

Position	
N	150°
X	140°
Y	130°
Z	120°

Jam-Nut Panel Cutouts

Shell Size	øA +.005 (.13) -.000 (.00)	B Flat ±.002 (.05)
7	.443 (11.25)	.426 (10.82)
8	.505 (12.83)	.481 (12.22)
9	.567 (14.40)	.539 (13.69)
10	.630 (16.00)	.612 (15.54)
12	.755 (19.18)	.719 (18.26)

Jam-Nut Dimensions

Shell Size	Ø A	B Flats	C Flats	D Thread
7	.670 (17.02)	.635 (16.13)	.411 (10.44)	.4375-28 UNEF-2A
8	.775 (19.68)	.735 (18.67)	.473 (12.01)	.5000-32 UN-2A
9	.875 (22.23)	.806 (20.47)	.530 (13.46)	.5625-32 UN-2A
10	.980 (24.89)	.940 (23.88)	.604 (15.34)	.6250-32 UN-2A
12	1.062 (26.97)	.986 (25.04)	.712 (18.08)	.7500-28 UN-2A

Material / finish:

- Shell, jam-nut: CRES / see How to Order Table
- Contacts: alloy 52 / gold plate
- Sockets: copper alloy / gold plate
- Seals: fluorosilicone / N.A.
- Insulator, hermetic: fused glass / N.A.
- Insulator, socket: high-grade dielectric / N.A.

Dimensions in Inches (millimeters) are subject to change without notice.