


FRD Type : KCF25A40

OUTLINE DRAWING

FEATURES

- * Similar to TO-247AC (TO-3P) Case
- * Dual Diodes – Cathode Common
- * Ultra – Fast Recovery
- * Low Forward Voltage Drop
- * High Surge Capability
- * 200 Volts thru 400 Volts Types Available



Maximum Ratings


Approx Net Weight:5.55g

Rating	Symbol	KCF25A40			Unit
Repetitive Peak Reverse Voltage	V _{RRM}	400			V
Non-repetitive Peak Reverse Voltage	V _{RSM}	440			V
Average Rectified Output Current	I _O	25	Tc=85℃	50 Hz,Full Sine Wave Resistive Load	A
RMS Forward Current	I _{F(RMS)}	28			A
Surge Forward Current	I _{FSM}	150	50 Hz Full Sine Wave,1cycle Non-repetitive		A
Operating JunctionTemperature Range	T _{jw}	- 40 to + 150			℃
Storage Temperature Range	T _{stg}	- 40 to + 150			℃
Mounting torque		0.5	Recommended value		N•m

Electrical • Thermal Characteristics

Characteristics	Symbol	Conditions	Min.	Typ.	Max.	Unit
Peak Reverse Current	I_{RM}	$T_j=25^{\circ}C, V_{RM}=V_{RRM}$ per Arm	-	-	50	μA
Peak Forward Voltage	V_{FM}	$T_j=25^{\circ}C, I_{FM}=12.5A$ per Arm	-	-	1.25	V
Reverse Recovery Time	t_{rr}	$I_{FM}=10 A$, $-di/dt= 50 A/\mu s$, $T_a= 25^{\circ}C$	-	-	50	ns
Thermal Resistance	$R_{th(j-c)}$	Junction to Case	-	-	2	$^{\circ}C/W$

KCF25A40 OUTLINE DRAWING (Dimensions in mm)



Center Tap

