







- 1 MATERIAL: CONNECTOR — NYLON UL94V-2 (YELLOW).
CONTACTS — 0.30[.012] THICK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 640600-2 THRU 2-640600-4]
(MATTE WHISKER MITIGATED TIN 0.00203[.000080] MIN
THICKNESS OVER NICKEL UNDERPLATE FOR
3-640600-2 THRU 5-640600-4).
- 2 CONTACTS ACCEPT 20 AWG WIRE WITH 2.41[.095] MAX INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 1.14 ± 0.03 [.045 $\pm$.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: FEED-THRU WITH LOCKING RAMP.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	95.10	[3.744]	24	5-640600-4
	91.14	[3.588]	23	5-640600-3
	87.17	[3.432]	22	5-640600-2
	83.21	[3.276]	21	5-640600-1
	79.25	[3.120]	20	5-640600-0
	75.29	[2.964]	19	4-640600-9
	71.32	[2.808]	18	4-640600-8
	67.36	[2.652]	17	4-640600-7
	63.40	[2.496]	16	4-640600-6
	59.44	[2.340]	15	4-640600-5
	55.47	[2.184]	14	4-640600-4
	51.51	[2.028]	13	4-640600-3
	47.55	[1.872]	12	4-640600-2
	43.59	[1.716]	11	4-640600-1
	39.62	[1.560]	10	4-640600-0
	35.66	[1.404]	9	3-640600-9
	31.70	[1.248]	8	3-640600-8
	27.74	[1.092]	7	3-640600-7
	23.77	[.936]	6	3-640600-6
	19.81	[.780]	5	3-640600-5
	15.85	[.624]	4	3-640600-4
	11.89	[.468]	3	3-640600-3
	7.92	[.312]	2	3-640600-2
SUPERSEDED 	95.10	[3.744]	24	2-640600-4
	91.14	[3.588]	23	2-640600-3
	87.17	[3.432]	22	2-640600-2
	83.21	[3.276]	21	2-640600-1
	79.25	[3.120]	20	2-640600-0
	75.29	[2.964]	19	1-640600-9
	71.32	[2.808]	18	1-640600-8
	67.36	[2.652]	17	1-640600-7
	63.40	[2.496]	16	1-640600-6
	59.44	[2.340]	15	1-640600-5
	55.47	[2.184]	14	1-640600-4
SUPERSEDED 	51.51	[2.028]	13	1-640600-3
	47.55	[1.872]	12	1-640600-2
	43.59	[1.716]	11	1-640600-1
	39.62	[1.560]	10	1-640600-0
	35.66	[1.404]	9	640600-9
	31.70	[1.248]	8	640600-8
 SUPERSEDED	27.74	[1.092]	7	640600-7
	23.77	[.936]	6	640600-6
	19.81	[.780]	5	640600-5
	15.85	[.624]	4	640600-4
	11.89	[.468]	3	640600-3
	7.92	[.312]	2	640600-2
	DIM A		NO OF CIRCUITS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWG B. LEWIS		12FEB91		 TE Connectivity					
			CHK R. SWING		12FEB91							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD D. CLARK		NAME					
		0 PLC ± -			PRODUCT SPEC		MTA-156 CONNECTOR ASSEMBLY, 20 AWG, STANDARD					
		1 PLC ± -			108-1051							
		2 PLC ± -			APPLICATION SPEC							
		3 PLC ± 0.13 [.005]			114-1020		SIZE					
		4 PLC ± -					CAGE CODE					
		ANGLES ± -					DRAWING NO					
MATERIAL		FINISH			WEIGHT		RESTRICTED TO					
					-		A2 00779 C-640600					
CUSTOMER DRAWING							SCALE		SHEET		REV	
							4:1		1 OF 1		1/1	