




- | | | | | | | | | | | |
|---|--------------------------------------|---|--|--------------|---------------------------------------|-----------|--|------------------------|---------------------------|--|
| CONVERT TO LEAD-FREE
EC NO: 2002/95-2078
DPMV1 BARRA 2012/11/26
CHICK-BINGHAM 2012/12/06
APPS-MILLER 2012/12/31 | QUALITY SYMBOLS
▽=0
▽=0
▽=0 | DESCRIPTION
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS | GENERAL TOLERANCES
(UNLESS SPECIFIED) | | DIMENSION STYLE
MM ONLY | | SCALE
4:1 | DESIGN UNITS
METRIC | THIRD ANGLE
PROJECTION | |
| | | | mm | INCH | DRAWN BY DATE
MSANDBERG 2007/19/07 | | TITLE
IMPACT 4 PAIR HEADER
LEFT GUIDED ASSEMBLY
SALES DRAWING | | | |
| | | | 4 PLACES ± | ± | CHECKED BY DATE
JLAURX 2007/19/07 | | | | | |
| | | | 3 PLACES ± | ± | APPROVED BY DATE
JLAURX 2010/11/15 | | | | | |
| | | | 2 PLACES ± | ± | | | | | | |
| 1 PLACE ± | ± | MATERIAL NO. | | DOCUMENT NO. | | SHEET NO. | | | | |
| | | | ANGULAR ±1/2° | | SEE TABLE | | SD-76155-002 | | 1 OF 3 | |
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | | | | | |


PART NUMBER TABLE

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	GUIDE LEFT END WALL OPTION
76155-*3**	6	24	19.3	9.50	
76155-*8**	8	32	23.1	13.30	
76155-*1**	10	40	26.9	17.10	
76155-*6**	16	64	38.3	28.50	



GUIDE LEFT
END WALL
OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	GUIDE LEFT OPEN WALL OPTION
76155-*3**	6	24	17.9	9.50	
76155-*8**	8	32	21.7	13.30	
76155-*1**	10	40	25.5	17.10	
76155-*6**	16	64	36.9	28.50	



GUIDE LEFT
OPEN WALL
OPTION

PART NUMBER LOGIC

76155-****


MODULE TYPE
3 = GUIDE LEFT, TIN
7 = GUIDE LEFT END WALL, TIN

PIN LENGTH (P)
3 = 4.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
4 = 4.90 (SHORT COMPLIANT, 0.46±0.05 PTH)
5 = 5.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
6 = 4.50 (MICRO COMPLIANT, 0.39±0.05 PTH)
7 = 4.90 (MICRO COMPLIANT, 0.39±0.05 PTH)
8 = 5.50 (MICRO COMPLIANT, 0.39±0.05 PTH)



OF COLUMNS
1 = 10 COL
3 = 6 COL
6 = 16 COL
8 = 8 COL

KEY ORIENTATION
0 = NO KEY
1 = A
2 = B
3 = C
4 = D
5 = E
6 = F
7 = G
8 = H

SEE SHEET 1 EC NO: UCP2013-2078 DRWN: TIBARRA 2012/11/26 CHKD: J BINGHAM 2012/12/18 APPR: SMILLER 2012/12/31	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	TITLE
						MM ONLY		3:1	METRIC		
						DRAWN BY DATE					
						CHECKED BY DATE					
						APPROVED BY DATE					
						MATERIAL NO.		DOCUMENT NO.			
						SEE TABLE		SD-76155-002			
						SIZE					



IMPACT 4 PAIR
BOARD RELATIONSHIPS



SEE SHEET 1 EC NO: UCP2013-2078 DRWN: TIBARRA 2012/11/26 CHKD: JB INGHAM 2012/12/18 APPR: SMILLER 2012/12/31	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	IMPACT 4 PAIR HEADER LEFT GUIDED ASSEMBLY SALES DRAWING molex DOCUMENT NO. SD-76155-002 SHEET NO. 3 OF 3	
			mm	INCH	DRAWN BY MSANDBERG	DATE 2007/19/07	TITLE				
			4 PLACES ± ---	± ---	CHECKED BY JLAURX	DATE 2007/19/07					
			3 PLACES ± ---	± ---	APPROVED BY JLAURX	DATE 2010/11/15					
			2 PLACES ± 0.13	± ---	MATERIAL NO.						
			1 PLACE ± 0.25	± ---							
			0 PLACE ±	±	SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
			ANGULAR ±1/2°		SIZE C						