

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

ES

00

P

LTR

DESCRIPTION

DATE

DWN

APVD





D

REVISED ECR-16-005069



07APR2016

T.Q

W.H



SECTION A-A



0.30	31.5	30.5	28.5	20	8-353908-0	2-353908-0
0.29	30.0	29.0	27.0	19	7-353908-9	1-353908-9
0.27	28.5	27.5	25.5	18	7-353908-8	1-353908-8
0.26	27.0	26.0	24.0	17	7-353908-7	1-353908-7
0.24	25.5	24.5	22.5	16	7-353908-6	1-353908-6
0.23	24.0	23.0	21.0	15	7-353908-5	1-353908-5
0.21	22.5	21.5	19.5	14	7-353908-4	1-353908-4
0.20	21.0	20.0	18.0	13	7-353908-3	1-353908-3
0.19	19.5	18.5	16.5	12	7-353908-2	1-353908-2
0.17	18.0	17.0	15.0	11	7-353908-1	1-353908-1
0.16	16.5	15.5	13.5	10	7-353908-0	1-353908-0
0.14	15.0	14.0	12.0	9	6-353908-9	353908-9
0.13	13.5	12.5	10.5	8	6-353908-8	353908-8
0.13	12.0	11.0	9.0	7	6-353908-7	353908-7
0.10	10.5	9.5	7.5	6	6-353908-6	353908-6
0.09	9.0	8.0	6.0	5	6-353908-5	353908-5
0.07	7.5	6.5	4.5	4	6-353908-4	353908-4
0.06	6.0	5.0	3.0	3	6-353908-3	353908-3
0.04	4.5	3.5	1.5	2	6-353908-2	353908-2
WEIGHT (g)	C	B	A	Pos	BLUE	WHITE
DIMENSIONS				P/N		


NOTES:

- △ APPLICABLE WIRE SIZE: AWG#24~#30(0.22mm²~0.05mm²).
INSULATION DIAMETER: 0.7mm~1.03mm.
- USE WITH RECEPTACLE CONTACT P/N
AWG#24~#28: 353907-1, 353918-1(L/P)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



GENERAL TOLERANCE

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

MATERIAL

66NYLON
UL94 V-0

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

WIRE RANGE



INSULATION DIA



DWN H.HOSHINO 26.APR.'97

CHK J.TANIGAWA 26.APR.'97

APVD S.KUBONOHI 10.MAR.'99

PRODUCT SPEC

108-60025

APPLICATION SPEC

114-5245

WEIGHT

CUSTOMER DRAWING



TE Connectivity

AMP MINI COMMON TERMINATED (CT)
CONNECTOR 1.5mm PITCH
HOUSING, CRIMP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=353908

SCALE NON

SHEET

1 of 2

REV





D

- , - .

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



0.30	31.5	30.5	28.5	20	4-353908-0
0.29	30.0	29.0	27.0	19	3-353908-9
0.27	28.5	27.5	25.5	18	3-353908-8
0.26	27.0	26.0	24.0	17	3-353908-7
0.24	25.5	24.5	22.5	16	3-353908-6
0.23	24.0	23.0	21.0	15	3-353908-5
0.21	22.5	21.5	19.5	14	3-353908-4
0.20	21.0	20.0	18.0	13	3-353908-3
0.19	19.5	18.5	16.5	12	3-353908-2
0.17	18.0	17.0	15.0	11	3-353908-1
0.16	16.5	15.5	13.5	10	3-353908-0
0.14	15.0	14.0	12.0	9	2-353908-9
0.13	13.5	12.5	10.5	8	2-353908-8
0.13	12.0	11.0	9.0	7	2-353908-7
0.10	10.5	9.5	7.5	6	2-353908-6
0.09	9.0	8.0	6.0	5	2-353908-5
0.07	7.5	6.5	4.5	4	2-353908-4
0.06	6.0	5.0	3.0	3	2-353908-3
0.04	4.5	3.5	1.5	2	2-353908-2
WEIGHT (g)	C	B	A	Pos	WHITE
	DIMENSIONS				P/N

SECTION A-A

NOTES:

- NOTES:
1. APPLICABLE WIRE SIZE: AWG#24~#30($0.22\text{mm}^2\sim 0.05\text{mm}^2$).
INSULATION DIAMETER: $0.7\text{mm}\sim 1.03\text{mm}$.
 2. USE WITH RECEPTACLE CONTACT P/N
AWG#24~#28: 353907-1, 353918-1(L/P)
 3. COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF
NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING
CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	26.APR.'97
-----	------------

H.HOSHINO	
CHK	26.APR.'97

J.TANIGAWA	10 MAR '88
------------	------------

APVD 10.MAR. 99
S.KUBONOH

PRODUCT SPEC	
--------------	--

108-60025

APPLICATION SPEC

114-5245

WEIGHT

CUSTOMER DRAWING

26.APR.'97

A. AOSHINO
CHK

26 APR '97

J.TANIGAWA

20:41 R. 57

APVD

S.KUBONOH
PRODUCT SPEC

PRODUCT SPEC

108-6

APPLICATION SPE

114-5

	1	1	0
WEIGHT			

CUSTOMER DRAWING



TE Connectivity

AMP MINI COMMON TERMINATED (CT)
CONNECTOR 1.5mm PITCH
HOUSING, CRIMP TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	©-353908	—

SCALE	NON	SHEET	3 OF 3	REV	D
-------	-----	-------	--------	-----	---

1470-19 (3/11)