




Home: Ring and Spade Terminals >

Part Number: 50855-7512

Ring Tongue Terminal for 12 AWG, Closed Un-insulated Brazed Barrel, Stud Size M10, Oxygen-Free Copper, Length 25.00mm



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	50855
Category:	Ring and Spade Terminals

[CHECK DISTRIBUTOR INVENTORY](#)

- [Add to My Parts](#)
- [Email this page](#)

[Go to Part Detail ▾](#)**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active [EU RoHS Certificate of Compliance \(PDF\)](#) [Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Hand Crimper For JIS Terminal	57257-5000
Air Type Hand Crimper For JIS Terminal	57343-9005

Crimp Quality Equipment[Molex also offers wire strippers, pull testers, shut-height gauges, micrometers and more](#)**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)**▼ General**

Status	Obsolete
Category	Ring and Spade Terminals
Series	50855
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800754838160

▼ Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1928.000/mg
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	M10
Termination Interface: Style	Crimp or Compression
Wire Size AWG	12

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

UL E134962

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

