

012

24.2±0.3

11.5±0.2

9.8±0.2

7.8±0.2

2- $\phi 6.0\pm 0.1$

2- $\phi 3.65\pm 0.05$

37.3±0.5

20.6±0.2

14.3±0.3

1

5

$\phi 6.0\pm 0.1$

0.8±0.2

$\phi 3.0\pm 0.05$

$\phi 3.5\pm 0.05$

A

B

C

INSIDE VIEW

												Approved		
												Check		
TITLE: 3.5MP TO 2*3.5MJ					Unless Specified,otherwise tolerance are +/-0.1mm; Remark:ROHS Requirement Applied(符合ROHS)									
NO	Description	Unit	Materials	Finish/Color	PART NO.	REV	DESCRIPTION	Issue	A	DATE:	2007/12/4	Drawn	李傑	
A.	3.5MJ	2	BRASS	NI		1						Unit	M/M	
B.	3.5MP	1	BRASS	NI		2						Scale	2:1	
C.	BODY	1	ABS	B		3								
D.														
E.														