







ELECTRICAL RATING

20A - 120, 240, 480 OR 600 VAC; 1/2 HP-120 VAC, 1HP-240 VAC

PILOT DUTY RATING: 600 VAC MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 		
CHARACTERISTICS PRETRAVEL ————— 17° MAX OVERTRAVEL ————— 58° MIN DIFFERENTIAL TRAVEL ————— 8° MAX TOTAL TRAVEL ————— (75°) OPERATING TORQUE ————— 4 IN. LBS MAX FULL TRAVEL TORQUE ————— 4 IN. LBS MAX		ELECTRICAL DATA CONTACT ARRANGEMENT DOUBLE POLE		SCALE NONE		
				DO NOT SCALE PRINT		
				UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
		DC VOLTAGE		120	240	ONE PLACE (.0) ± .030
		MAKE AND BREAK INDUCTIVE		1.10	1.50	TWO PLACE (.00) ± .015
		RESISTIVE		1.50	0.75	THREE PLACE (.000) ± .005
						ANGLES ±
						WEIGHT

- NOTES
- 1 - SWITCH HEAD MOUNTS IN ANY OF FOUR POSITIONS
 - 2 - LEVER ADJUSTABLE IN 10° INCREMENTS
 - 3 - ZINC HOUSING FINISHED IN EPOXY PAINT
 - 4 - SWITCH WILL WITHSTAND 4000 VDC MINIMUM DIELECTRIC CHECK BETWEEN OPEN TERMINALS 3-4 AND 7-8 WITH LEVER IN FREE POSITION AND BETWEEN TERMINALS 1-2 AND 5-6 WITH LEVER IN OPERATED POSITION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[LSQ051](#)