





D

C


B

A



PC BOARD LAYOUT

- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 POST MATERIAL: COPPER ALLOY.
- 3 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 5 PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.
- 6 MARKING ON THIS SIDE.



SECTION X-X

1,16	2-15	16	B	5148103-1
1,16	2-15	16	A	
POSITIONS LOADED WITH 4.93 [.194] CONTACTS	POSITIONS LOADED WITH 4.16 [.164] CONTACTS	NO. OF LOADED POSITIONS	ROW	ASSY PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE CHK A. SHARPE APVD A. SHARPE	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC WEIGHT -	ASSEMBLY, PIN, EUROCARD, TYPE 1/2B, 32 POSITION, 2.64 [.104] SOLDER POST WITH MFBL CONTACTS	
MATERIAL 1 2		FINISH 3	SIZE A1	RESTRICTED TO
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV 01