



Terminal blocks

to Type 020

-  **Type 009** page 93
-  **Type 026** page 129
-  **Type 049** page 93


to Type 320

-  **ASP045** page 49
-  **Type 313** page 96
-  **Type 314** page 96
-  **Type 349** page 94
-  **Type 350** page 94

Accessories

for **Type 320**
Coding set
700024

page 206



Type 020


Header, centerline 5 mm / 0.197 inches, vertical mounting, round contact pins 1.3 mm / 0.051 inches, closed ends

Technical Data

 V / A	300 / 15		
 V / A	300 / 15		
	250 V / 4 kV / 10 A		
Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 3.7 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250	630	630
Rated test voltage	2.5	6	4
Protection category according to IEC 529			
	IP00		
Solder pin dimension	1 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	5.2 mm		
Pole size	2 - 22		
Color	black		

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 6.6 \text{ mm} / 0.260 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 020

centerline 5 mm / 0.197 inches

P/N 310201

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22		

Type 020


centerline 10 mm / 0.394 inches

P/N 310202

	02	03	04	05	06	07	08
09	10	11					

 Standard pole sizes

 Available on demand. Minimum order quantity 5000 pieces per item.



Type 320


Header, centerline 5 mm / 0.197 inches, vertical square contact pins 1 mm / 0.039 inches, closed ends, codable

Technische Daten

 V / A	300 / 15		
	320 V / 4 kV / 10 A		
Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 4 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	320	800	800
Rated test voltage	4	6	4
Protection category according to IEC 529			
	IP00		
Solder pin dimension	1.0 x 1.0 mm		
Recommended pc board hole dia.	Ø 1.5 mm		
Solder pin length	3.25 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 6.6 \text{ mm} / 0.260 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 320

centerline 5 mm / 0.197 inches

P/N 313201

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

 Standard pole sizes

 Available on demand. Minimum order quantity 5000 pieces per item.