

LOW CURRENT HEV FUSE

RoHS



Description

The LC HEV fuse is designed for protection of high-voltage accessory circuits in electric and hybrid electric vehicles.

Specifications

Voltage Rating (10A, 15A, 20A, 30A):	450 VDC
Voltage Rating (40A):	425 VDC
Interrupting Rating (10A, 15A, 20A, 30A):	10kA @ 450 VDC
Interrupting Rating (40A):	10kA @ 425 VDC
Operating Temperature Range:	-40°C to +125°C


Ordering Information

Part Number	Termination	Package Size
0HEVxxx.ZXC	Cartridge	225
0HEVxxx.ZXISO	Bolt Down (ISO)	168
0HEVxxx.ZXPY	Blade	144
0HEVxxx.ZXBD	Bolt Down (Axial)	144
0HEVxxx.ZXPCB	PCB Mount	168
0HEVxxx.ZXPCBL	PCB Mount (Long)	168

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s) 10A	Opening Time Min / Max (s) 15A, 20A, 30A	Opening Time Min / Max (s) 40A
100	100 hrs / -	100 hrs / -	100 hrs / -
110	4 hrs / -	4 hrs / -	-
135	100 / 3600	150 / 3600	150 / 3600
150	10 / 1000	10 / 1000	10 / 1000
200	0.5 / 100	0.5 / 100	0.5 / 100
300	0.1 / 15	0.1 / 15	0.1 / 15
500	0.05 / 1	0.05 / 1	0.05 / 1

Time-Current Characteristic Curves



Ratings

Part Number	Current Rating	Color Code	Typical Voltage Drop at 70% I _R	Maximum Voltage Drop Spec at 100% I _R	Typical Cold Resistance	Minimum Melting I ² t
0HEV010.xxx	10A	■	114 mV	300 mV	12.8 mOhm	255 A²s
0HEV015.xxx	15A	■	96 mV	200 mV	7.9 mOhm	133 A²s
0HEV020.xxx	20A	■	79 mV	200 mV	5.0 mOhm	268 A²s
0HEV030.xxx	30A	■	67 mV	200 mV	2.7 mOhm	993 A²s
0HEV040.xxx	40A	■	69 mV	200 mV	2.0 mOhm	1495 A²s

(Average Initial Measurements)


LOW CURRENT HEV FUSE

RoHS


Dimensions

Dimensions in mm


ZXC Type:




ZXISO Type:




ZXPY Type:



ZXBD Type:



ZXPCB Type:



ZXPCBL Type:

