








- 1 WIRE RANGE: 0.12–0.9mm² (26–18 AWG).
- 2 INSULATION RANGE: 1.27–2.92 [.050–.115] MAX. DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- △ TIP PLATE WITH 0.00076–0.00091 [.000030–.000036] MIN GOLD IN THE LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

△ GOLD PLATE	0.20 [.008] PHOS BRZ	350967-2
PRE-TIN	0.20 [.008] PHOS BRZ	350967-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN K. SALMON	3-21-95	STE TE Connectivity	
DIMENSIONS: MM(INCHES)		CHK R. SWING	3-21-95		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. LONG	MR PIN	
	0 PLC ± -		PRODUCT SPEC		
	1 PLC ± -		APPLICATION SPEC		
	2 PLC ± -		WEIGHT		
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A1	
				CAGE CODE 00779	
				DRAWING NO C-350967	
				RESTRICTED TO	
				CUSTOMER DRAWING	
				SCALE 5:1	
				SHEET 1	
				OF 1	
				REV L1	