


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
04/02/05	A	ADDED MATERIAL SPECS	T.B.	B.S.	
05/14/05	B	ADDED TOTAL WIRE LENGTH	T.B.	B.S.	
02/29/08	C	ADDED " ROHS COMPLIANT"	T.B.	B.S.	
07/29/11	D	ADDED MELTING POINT NOTE MTL. NYLON 6 WAS NYLON	T.B.	B.S.	
05/04/12	E	UPDATED LEAD WIRE NOTE	T.B.	B.S.	



NOTES:

- MATERIAL:
HOUSING : NYLON 6, UL 94V-2, FILE NO. E338653
- LEAD WIRE IN LOOP: 16AWG, UL-CSA, 105°C, UL1015, 600V,
TOTAL LENGTH 8.125"
- MAXIMUM CURRENT: 10A
- MELTING POINT: 200°C
- INSULATION RESISTANCE AT 500V DC: 100M Ω MIN
- CONTACT RESISTANCE: 5M Ω AT 1A DC
- DIELECTRIC STRENGTH FOR 60 SECONDS: AC 1500V MIN
ROHS COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal $\pm .5$ (.020)		Scale	Drawn By B.S.
			Approved By T.B.
Fractional $\pm .8$ (.030)	Title FUSED POWER CORD W/PLASTIC INLINE FUSE HOLDER		
Angular $\pm 3^\circ$	Date 05/04/12	Drawing Number BF303	