




- 1 HOUSING: PBT, UL 94V-0 RATED, COLOR-BLACK
CONTACTS: COPPER ALLOY PER ASTM B103
- 2 MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- 3 0.00076[.000030] MIN GOLD IN CONTACT AREA, 0.00127-0.00254 [.000050-.000100]
TIN-LEAD IN AREA E, ALL OVER 0.00127[.000050] MIN NICKEL.
- 4 0.00076[.000030] MIN GOLD IN CONTACT AREA, 0.00127-0.00254 [.000050-.000100]
TIN IN AREA E, ALL OVER 0.00127[.000050] MIN NICKEL.
5. USE WITH #20-#22 AWG WIRE SIZE, .050 MAX INSULATION DIA.,
.015 MAX INSULATION WALL THICKNESS.
- 6 CONTACT IDENTIFICATION NUMBER "3" LOCATED IN THIS AREA.
- 7 AMP TRADEMARK (EITHER SIDE).
- 8 OBSOLETE PART NUMBER.
- 9 ROHS 2002/95/EC COMPLIANT.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

10	OBSOLETE	 	81.28 [3.200]	31	64	8-102448-0
10	OBSOLETE	 	76.20 [3.000]	29	60	7-102448-8
		 	63.50 [2.500]	24	50	7-102448-3
		 	50.80 [2.000]	19	40	6-102448-8
		 	43.18 [1.700]	16	34	6-102448-5
10	OBSOLETE	 	40.64 [1.600]	15	32	6-102448-4
		 	38.10 [1.500]	14	30	6-102448-3
10	OBSOLETE	 	35.56 [1.400]	13	28	6-102448-2
		 	33.02 [1.300]	12	26	6-102448-1
		 	30.48 [1.200]	11	24	6-102448-0
10	OBSOLETE	 	27.94 [1.100]	10	22	5-102448-9
		 	25.40 [1.000]	9	20	5-102448-8
		 	22.86 [.900]	8	18	5-102448-7
10	OBSOLETE	 	20.32 [.800]	7	16	5-102448-6
		 	17.78 [.700]	6	14	5-102448-5
		 	15.24 [.600]	5	12	5-102448-4
		 	12.70 [.500]	4	10	5-102448-3
		 	10.16 [.400]	3	8	5-102448-2
10	OBSOLETE	 	7.62 [.300]	2	6	5-102448-1
		FINISH	B	A	NO. OF POSN	PART NO.

	SUPERSEDED BY 1-102448-8		91.44 [3.600]	35	72		3-102448-4
	SUPERSEDED BY 1-102448-3		88.90 [3.500]	34	70		3-102448-3
	SUPERSEDED		86.36 [3.400]	33	68		3-102448-2
	SUPERSEDED		83.82 [3.300]	32	66		3-102448-1
	OBSELETE		81.28 [3.200]	31	64		3-102448-0
	SUPERSEDED BY 1-102448-3		78.74 [3.100]	30	62		2-102448-9
	OBSELETE		76.20 [3.000]	29	60		2-102448-8
	SUPERSEDED BY 1-102448-3		73.66 [2.900]	28	58		2-102448-7
	SUPERSEDED		71.12 [2.800]	27	56		2-102448-6
	SUPERSEDED BY 1-102448-1		68.58 [2.700]	26	54		2-102448-5
	SUPERSEDED BY 1-102448-1		66.04 [2.600]	25	52		2-102448-4
			63.50 [2.500]	24	50		2-102448-3
	SUPERSED BY 1-102448-0		60.96 [2.400]	23	48		2-102448-2
	SUPERSED BY 1-102448-0		58.42 [2.300]	22	46		2-102448-1
	SUPERSEDED		55.88 [2.200]	21	44		2-102448-0
	SUPERSEDED BY 102448-8		53.34 [2.100]	20	42		1-102448-9
			50.80 [2.000]	19	40		1-102448-8
	SUPERSEDED BY 102448-7		48.26 [1.900]	18	38		1-102448-7
	SUPERSEDED BY 102448-7		45.72 [1.800]	17	36		1-102448-6
	SUPERSEDED BY 6-102448-5		43.18 [1.700]	16	34		1-102448-5
	OBSELETE		40.64 [1.600]	15	32		1-102448-4
			38.10 [1.500]	14	30		1-102448-3
	OBSELETE		35.56 [1.400]	13	28		1-102448-2
			33.02 [1.300]	12	26		1-102448-1
			30.48 [1.200]	11	24		1-102448-0
	OBSELETE		27.94 [1.100]	10	22		102448-9
			25.40 [1.000]	9	20		102448-8
			22.86 [.900]	8	18		102448-7
			20.32 [.800]	7	16		102448-6
			17.78 [.700]	6	14		102448-5
			15.24 [.600]	5	12		102448-4
			12.70 [.500]	4	10		102448-3
	SUPERSEDED BY 5-102448-2		10.16 [.400]	3	8		102448-2
	OBSELETE		7.62 [.300]	2	6		102448-1
		FINISH	B	A	NO. OF POSN		PART NO.