




# SPADE TONGUE (A type) Non-insulated



Actual

Refer to page 145 for  
actual size of the terminal.  
(except for 1.25-2A)





File No.: E42024 LR20812

| Applicable Wire<br>AWG#(mm <sup>2</sup> ) | Stud size |        | Part No.   | Standard | Dimensions mm (in.) |             |              |             |            |            |                  |            | Tool No.                                     | Qty/box |
|-------------------------------------------|-----------|--------|------------|----------|---------------------|-------------|--------------|-------------|------------|------------|------------------|------------|----------------------------------------------|---------|
|                                           | American  | Metric |            |          | d <sub>2</sub>      | B           | L            | F           | E          | ø D        | ø d <sub>1</sub> | T          |                                              |         |
| 26 to 22<br>(0.2 to 0.5)                  | 1-2       | 2      | 0.5-2A     |          | 2.2 (.087)          | 4.6 (.181)  | 12.8 (.504)  | 4.5 (.177)  | 4.0 (.157) | 2.0 (.079) | 1.0 (.039)       | 0.5 (.020) | YHT-2622<br>YA-1<br>YA-2<br>BCT-0514         | 1,000   |
|                                           | 3-4       | 3      | 0.5-3A     |          | 3.2 (.126)          | 5.0 (.197)  | 12.5 (.492)  | 6.0 (.236)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 0.5-3.7A   |          | 3.7 (.146)          | 6.4 (.252)  | 15.0 (.591)  | 7.7 (.303)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 0.5-4A     |          | 4.3 (.169)          | 7.0 (.276)  | 16.2 (.638)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
| 22 to 16<br>(0.25 to 1.65)                | 1-2       | 2      | 1.25-2A    |          | 2.2 (.087)          | 4.6 (.181)  | 14.6 (.575)  | 4.3 (.169)  | 4.8 (.189) | 3.4 (.134) | 1.7 (.067)       | 0.8 (.031) | YHT-2210<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | 1.25-C3A   |          | 3.2 (.126)          | 5.6 (.221)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 3-4       | 3      | 1.25-B3A   |          | 3.2 (.126)          | 5.8 (.228)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 3-4       | 3      | 1.25-M3A   |          | 3.2 (.126)          | 6.35 (.250) | 16.0 (.630)  | 8.0 (.315)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-C3.5A |          | 3.7 (.146)          | 5.6 (.221)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-B3.5A |          | 3.7 (.146)          | 5.8 (.228)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-N3A   |          | 3.7 (.146)          | 6.2 (.244)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-YS3A  |          | 3.7 (.146)          | 6.4 (.252)  | 15.4 (.606)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-S3A   |          | 3.7 (.146)          | 7.2 (.283)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 1.25-P3A   |          | 3.7 (.146)          | 7.5 (.295)  | 13.8 (.543)  | 5.5 (.217)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 1.25-YS4A  |          | 4.3 (.169)          | 6.4 (.252)  | 15.4 (.606)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 1.25-S4A   |          | 4.3 (.169)          | 7.2 (.283)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 1.25-4A    |          | 4.3 (.169)          | 8.5 (.335)  | 15.8 (.622)  | 7.0 (.276)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 1.25-S5A   |          | 5.3 (.209)          | 7.2 (.283)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 1.25-M5A   |          | 5.3 (.209)          | 8.5 (.335)  | 15.8 (.622)  | 7.0 (.276)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 1.25-5A    |          | 5.3 (.209)          | 9.5 (.374)  | 15.8 (.622)  | 7.0 (.276)  |            |            |                  |            |                                              |         |
|                                           | 1/4       | 6      | 1.25-6A    |          | 6.4 (.252)          | 12.0 (.472) | 22.0 (.866)  | 11.0 (.433) |            |            |                  |            |                                              |         |
| 16 to 14<br>(1.04 to 2.63)                | 3-4       | 3      | 2-N3A      |          | 3.2 (.126)          | 5.9 (.232)  | 15.8 (.622)  | 6.3 (.248)  | 4.8 (.189) | 4.1 (.161) | 2.3 (.091)       | 0.8 (.031) | YHT-2210<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | 2-M3A      |          | 3.2 (.126)          | 6.0 (.236)  | 14.5 (.571)  | 5.0 (.197)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 2-C3.5A    |          | 3.7 (.146)          | 5.6 (.220)  | 15.8 (.622)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 2-YS3A     |          | 3.7 (.146)          | 6.4 (.252)  | 15.4 (.606)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 2-S3A      |          | 3.7 (.146)          | 7.2 (.283)  | 16.0 (.630)  | 6.5 (.256)  |            |            |                  |            |                                              |         |
|                                           | 5-6       | 3.5    | 2-3A       |          | 3.7 (.146)          | 8.5 (.335)  | 16.8 (.661)  | 7.3 (.287)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 2-YS4A     |          | 4.3 (.169)          | 6.4 (.252)  | 15.4 (.606)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 2-YM4A     |          | 4.3 (.169)          | 6.8 (.268)  | 15.4 (.606)  | 6.3 (.248)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 2-S4A      |          | 4.3 (.169)          | 7.2 (.283)  | 16.0 (.630)  | 6.5 (.256)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 2-4A       |          | 4.3 (.169)          | 8.5 (.335)  | 16.8 (.661)  | 7.3 (.287)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 2-M5A      |          | 5.3 (.209)          | 8.5 (.335)  | 16.8 (.661)  | 7.3 (.287)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 2-5A       |          | 5.3 (.209)          | 9.5 (.374)  | 16.8 (.661)  | 7.3 (.287)  |            |            |                  |            |                                              |         |
|                                           | 1/4       | 6      | 2-6A       |          | 6.4 (.252)          | 12.0 (.472) | 22.0 (.866)  | 11.0 (.433) |            |            |                  |            |                                              |         |
| 12 to 10<br>(2.63 to 6.64)                | 5-6       | 3.5    | 5.5-S3A    |          | 3.7 (.146)          | 7.2 (.283)  | 19.5 (.768)  | 7.5 (.295)  | 6.8 (.268) | 5.6 (.220) | 3.4 (.134)       | 1.0 (.039) | YHT-2210<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 5-6       | 3.5    | 5.5-3A     |          | 3.7 (.146)          | 9.5 (.374)  | 19.5 (.768)  | 7.5 (.295)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 5.5-S4A    |          | 4.3 (.169)          | 8.5 (.335)  | 19.5 (.768)  | 7.5 (.295)  |            |            |                  |            |                                              |         |
|                                           | 8         | 4      | 5.5-4A     |          | 4.3 (.169)          | 9.5 (.374)  | 19.5 (.768)  | 7.5 (.295)  |            |            |                  |            |                                              |         |
|                                           | 10        | 5      | 5.5-5A     |          | 5.3 (.209)          | 9.5 (.374)  | 19.5 (.768)  | 7.5 (.295)  |            |            |                  |            |                                              |         |
|                                           | 1/4       | 6      | 5.5-6A     |          | 6.4 (.252)          | 13.5 (.532) | 25.5 (1.004) | 12.2 (.480) |            |            |                  |            |                                              |         |
|                                           | 5/16      | 8      | 5.5-8A     |          | 8.4 (.331)          | 13.5 (.532) | 25.5 (1.004) | 12.2 (.480) |            |            |                  |            |                                              | 500     |

Note:1) The part numbers indicated in the above table are for products with a brazed seam.

When ordering products with a butted seam, add the prefix "WS" to the part number (ex. 2-4A → **WS2-4A**).

2) Delivery lead times may vary depending on the product. Contact JST for details.

**SPADE TONGUE (A type)** Vinyl-insulated

File No.: E42024 LR20812

| Applicable Wire<br>AWG#(mm <sup>2</sup> ) | Stud size |        | Part No.    |             | Standard | Dimensions mm (in.) |             |              |             |                |               |               |               | Color  | Tool No.                                     | Qty/box |
|-------------------------------------------|-----------|--------|-------------|-------------|----------|---------------------|-------------|--------------|-------------|----------------|---------------|---------------|---------------|--------|----------------------------------------------|---------|
|                                           | American  | Metric | Straight    | Flared      |          | d <sub>2</sub>      | B           | L            | F           | ℓ              | ø D           |               | T             |        |                                              |         |
| 26 to 22<br>(0.2 to 0.5)                  | 3-4       | 3      | V0.5-3A     | FV0.5-3A    |          | 3.2 (.126)          | 5.0 (.197)  | 16.5 (.650)  | 6.0 (.236)  | 8.0            | 1.9           | 2.9           | 0.5           | Yellow | YNT-2622<br>YA-1, YA-2<br>BCT-0514           | 1,000   |
|                                           | 5-6       | 3.5    | V0.5-3.7A   | FV0.5-3.7A  |          | 3.7 (.146)          | 6.4 (.252)  | 19.0 (.748)  | 7.7 (.303)  | (.315)         | (.075)        | (.114)        | (.020)        |        |                                              |         |
| 22 to 16<br>*(0.25 to 1.65)               | 1-2       | 2      | V1.25-2A    | FV1.25-2A   |          | 2.2 (.087)          | 4.6 (.181)  | 18.8 (.740)  | 4.3 (.169)  | 9.0<br>(.354)  | 3.2<br>(.126) | 4.0<br>(.157) | 0.8<br>(.031) | Red    | YNT-2216<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | V1.25-B3A   | FV1.25-B3A  |          | 3.2 (.126)          | 5.8 (.228)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V1.25-C3.5A | —           |          | 3.7 (.146)          | 5.6 (.220)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V1.25-N3A   | FV1.25-N3A  |          | 3.7 (.146)          | 6.2 (.244)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V1.25-YS3A  | FV1.25-YS3A |          | 3.7 (.146)          | 6.4 (.252)  | 19.6 (.772)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V1.25-S3A   | FV1.25-S3A  |          | 3.7 (.146)          | 7.2 (.284)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V1.25-P3A   | FV1.25-P3A  |          | 3.7 (.146)          | 7.5 (.295)  | 18.0 (.709)  | 5.5 (.217)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V1.25-YS4A  | FV1.25-YS4A |          | 4.3 (.169)          | 6.4 (.252)  | 19.6 (.772)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V1.25-S4A   | FV1.25-S4A  |          | 4.3 (.169)          | 7.2 (.284)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V1.25-4A    | FV1.25-4A   |          | 4.3 (.169)          | 8.5 (.335)  | 20.0 (.787)  | 7.0 (.276)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V1.25-S5A   | FV1.25-S5A  |          | 5.3 (.209)          | 7.2 (.284)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V1.25-M5A   | FV1.25-M5A  |          | 5.3 (.209)          | 8.5 (.335)  | 20.0 (.787)  | 7.0 (.276)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V1.25-5A    | FV1.25-5A   |          | 5.3 (.209)          | 9.5 (.374)  | 20.0 (.787)  | 7.0 (.276)  |                |               |               |               |        |                                              |         |
| 16 to 14<br>(1.04 to 2.63)                | 1/4       | 6      | V1.25-6A    | FV1.25-6A   |          | 6.4 (.252)          | 12.0 (.472) | 26.2 (1.032) | 11.0 (.433) | 9.0<br>(.354)  | 3.9<br>(.154) | 4.5<br>(.177) | 0.8<br>(.031) | Blue   | YNT-1614<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | V2-N3A      | FV2-N3A     |          | 3.2 (.126)          | 5.9 (.232)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 3-4       | 3      | V2-M3A      | FV2-M3A     |          | 3.2 (.126)          | 6.0 (.236)  | 18.7 (.736)  | 5.0 (.197)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V2-YS3A     | FV2-YS3A    |          | 3.7 (.146)          | 6.4 (.252)  | 19.6 (.772)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V2-S3A      | FV2-S3A     |          | 3.7 (.146)          | 7.2 (.284)  | 20.2 (.795)  | 6.5 (.256)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V2-3A       | FV2-3A      |          | 3.7 (.146)          | 8.5 (.335)  | 21.0 (.827)  | 7.3 (.287)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V2-YS4A     | FV2-YS4A    |          | 4.3 (.169)          | 6.4 (.252)  | 19.6 (.772)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V2-YM4A     | FV2-YM4A    |          | 4.3 (.169)          | 6.8 (.268)  | 19.6 (.772)  | 6.3 (.248)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V2-S4A      | FV2-S4A     |          | 4.3 (.169)          | 7.2 (.284)  | 20.2 (.795)  | 6.5 (.256)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V2-4A       | FV2-4A      |          | 4.3 (.169)          | 8.5 (.335)  | 21.0 (.827)  | 7.3 (.287)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V2-M5A      | FV2-M5A     |          | 5.3 (.209)          | 8.5 (.335)  | 21.0 (.827)  | 7.3 (.287)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V2-5A       | FV2-5A      |          | 5.3 (.209)          | 9.5 (.374)  | 21.0 (.827)  | 7.3 (.287)  |                |               |               |               |        |                                              |         |
| 12 to 10<br>(2.63 to 6.64)                | 1/4       | 6      | V2-6A       | FV2-6A      |          | 6.4 (.252)          | 12.0 (.472) | 26.2 (1.032) | 11.0 (.433) | 13.5<br>(.531) | 5.4<br>(.213) | 6.8<br>(.268) | 1.0<br>(.039) | Yellow | YNT-1210S<br>YA-4<br>BCT-0514                | 500     |
|                                           | 5-6       | 3.5    | V5.5-S3A    | FV5.5-S3A   |          | 3.7 (.146)          | 7.2 (.283)  | 26.2 (1.032) | 7.5 (.295)  |                |               |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | V5.5-3A     | FV5.5-3A    |          | 3.7 (.146)          | 9.5 (.374)  | 26.2 (1.032) | 7.5 (.295)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V5.5-S4A    | FV5.5-S4A   |          | 4.3 (.169)          | 8.5 (.335)  | 26.2 (1.032) | 7.5 (.295)  |                |               |               |               |        |                                              |         |
|                                           | 8         | 4      | V5.5-4A     | FV5.5-4A    |          | 4.3 (.169)          | 9.5 (.374)  | 26.2 (1.032) | 7.5 (.295)  |                |               |               |               |        |                                              |         |
|                                           | 10        | 5      | V5.5-5A     | FV5.5-5A    |          | 5.3 (.209)          | 9.5 (.374)  | 26.2 (1.032) | 7.5 (.295)  |                |               |               |               |        |                                              |         |
|                                           | 1/4       | 6      | V5.5-6A     | FV5.5-6A    |          | 6.4 (.252)          | 13.5 (.532) | 32.2 (1.268) | 12.2 (.480) |                |               |               |               |        |                                              |         |
|                                           | 5/16      | 8      | V5.5-8A     | FV5.5-8A    |          | 8.4 (.331)          | 13.5 (.532) | 32.2 (1.268) | 12.2 (.480) |                |               |               |               |        |                                              |         |

Note: 1) \*The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm<sup>2</sup>.Examples: If the cross-sectional area of the wire is 0.3mm<sup>2</sup>, fold the wire in two when crimping the terminal.If the cross-sectional area of the wire is 0.5mm<sup>2</sup>, crimp the terminal onto the wire as it is.

2) The part numbers indicated in the above table are for products with a brazed seam.



When ordering products with a butted seam, add the prefix "WS" to the part number (ex. V2-4A → **VWS2-4A**).3) To order products with nylon insulation, change the "V" in the part number prefix to "N" (ex. V2-4A → **N2-4A**).

Because nylon absorbs moisture, care must be taken concerning storage.

4) Delivery lead times may vary depending on the product. Contact JST for details.



# SPADE TONGUE (A type) Vinyl-insulated (funnel-entry)



File No.: E42024 LR20812


| Applicable Wire<br>AWG#(mm <sup>2</sup> ) | Stud size |        | Part No.     | Standard | Dimensions mm (in.) |             |              |             |                |               |               | Color  | Tool No.                                                 | Qty/box |
|-------------------------------------------|-----------|--------|--------------|----------|---------------------|-------------|--------------|-------------|----------------|---------------|---------------|--------|----------------------------------------------------------|---------|
|                                           | American  | Metric |              |          | d <sub>2</sub>      | B           | L            | F           | ℓ              | øD            | T             |        |                                                          |         |
| 22 to 16<br>*(0.25 to 1.65)               | 3-4       | 3      | FVX1.25-B3A  |          | 3.2 (.126)          | 5.8 (.228)  | 21.8 (.858)  | 6.3 (.248)  | 10.8<br>(.425) | 4.0<br>(.157) | 0.8<br>(.031) | Red    | YNT-2216<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514             | 1,000   |
|                                           | 5-6       | 3.5    | FVX1.25-N3A  |          | 3.7 (.146)          | 6.2 (.244)  | 21.8 (.858)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX1.25-YS3A |          | 3.7 (.146)          | 6.4 (.252)  | 21.4 (.843)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX1.25-S3A  |          | 3.7 (.146)          | 7.2 (.284)  | 21.8 (.858)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX1.25-P3A  |          | 3.7 (.146)          | 7.5 (.295)  | 21.8 (.858)  | 5.5 (.217)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX1.25-YS4A |          | 4.3 (.169)          | 6.4 (.252)  | 21.4 (.843)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX1.25-S4A  |          | 4.3 (.169)          | 7.2 (.284)  | 21.8 (.858)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX1.25-4A   |          | 4.3 (.169)          | 8.5 (.335)  | 21.8 (.858)  | 7.0 (.276)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX1.25-S5A  |          | 5.3 (.209)          | 7.2 (.284)  | 21.8 (.858)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX1.25-M5A  |          | 5.3 (.209)          | 8.5 (.335)  | 21.8 (.858)  | 7.0 (.276)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX1.25-5A   |          | 5.3 (.209)          | 9.5 (.374)  | 21.8 (.858)  | 7.0 (.276)  |                |               |               |        |                                                          |         |
| 16 to 14<br>(1.04 to 2.63)                | 1/4       | 6      | FVX1.25-6A   |          | 6.4 (.252)          | 12.0 (.472) | 28.0 (1.102) | 11.0 (.433) |                |               |               |        |                                                          |         |
|                                           | 3-4       | 3      | FVX2-N3A     |          | 3.2 (.126)          | 5.9 (.232)  | 21.8 (.858)  | 6.3 (.248)  | 10.8<br>(.425) | 4.6<br>(.181) | 0.8<br>(.031) | Blue   | BCT-0514<br>YNT-1614<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | FVX2-M3A     |          | 3.2 (.126)          | 6.0 (.236)  | 20.5 (.807)  | 5.0 (.197)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX2-YS3A    |          | 3.7 (.146)          | 6.4 (.252)  | 21.4 (.843)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX2-S3A     |          | 3.7 (.146)          | 7.2 (.284)  | 23.0 (.906)  | 6.5 (.256)  |                |               |               |        |                                                          |         |
|                                           | 5-6       | 3.5    | FVX2-3A      |          | 3.7 (.146)          | 8.5 (.335)  | 22.8 (.898)  | 7.3 (.287)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX2-YS4A    |          | 4.3 (.169)          | 6.4 (.252)  | 21.4 (.843)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX2-YM4A    |          | 4.3 (.169)          | 6.8 (.268)  | 21.4 (.843)  | 6.3 (.248)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX2-S4A     |          | 4.3 (.169)          | 7.2 (.284)  | 23.0 (.906)  | 6.5 (.256)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX2-4A      |          | 4.3 (.169)          | 8.5 (.335)  | 22.8 (.898)  | 7.3 (.287)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX2-M5A     |          | 5.3 (.209)          | 8.5 (.335)  | 22.8 (.898)  | 7.3 (.287)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX2-5A      |          | 5.3 (.209)          | 9.5 (.374)  | 22.8 (.898)  | 7.3 (.287)  |                |               |               |        |                                                          |         |
|                                           | 1/4       | 6      | FVX2-6A      |          | 6.4 (.252)          | 12.0 (.472) | 28.0 (1.102) | 11.0 (.433) |                |               |               |        |                                                          | 500     |
| 12 to 10<br>(2.63 to 6.64)                | 5-6       | 3.5    | FVX5.5-S3A   |          | 3.7 (.146)          | 7.2 (.284)  | 26.7 (1.051) | 7.5 (.295)  | 14.0<br>(.551) | 6.8<br>(.268) | 1.0<br>(.039) | Yellow | YNT-1210S<br>YA-4<br>BCT-0514                            | 500     |
|                                           | 5-6       | 3.5    | FVX5.5-3A    |          | 3.7 (.146)          | 9.5 (.374)  | 26.7 (1.051) | 7.5 (.295)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX5.5-S4A   |          | 4.3 (.169)          | 8.5 (.335)  | 26.7 (1.051) | 7.5 (.295)  |                |               |               |        |                                                          |         |
|                                           | 8         | 4      | FVX5.5-4A    |          | 4.3 (.169)          | 9.5 (.374)  | 26.7 (1.051) | 7.5 (.295)  |                |               |               |        |                                                          |         |
|                                           | 10        | 5      | FVX5.5-5A    |          | 5.3 (.209)          | 9.5 (.374)  | 26.7 (1.051) | 7.5 (.295)  |                |               |               |        |                                                          |         |
|                                           | 1/4       | 6      | FVX5.5-6A    |          | 6.4 (.252)          | 13.5 (.532) | 32.7 (1.287) | 12.2 (.480) |                |               |               |        |                                                          |         |
|                                           | 5/16      | 8      | FVX5.5-8A    |          | 8.4 (.331)          | 13.5 (.532) | 32.7 (1.287) | 12.2 (.480) |                |               |               |        |                                                          | 250     |

Note:1) The part numbers indicated in the above table are for products with a brazed seam.



When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVX2-4A → FVXWS2-4A).

2) \*The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm<sup>2</sup>.Examples: If the cross-sectional area of the wire is 0.3mm<sup>2</sup>, fold the wire in two when crimping the terminal.If the cross-sectional area of the wire is 0.5mm<sup>2</sup>, crimp the terminal onto the wire as it is.

3) Delivery lead times may vary depending on the product. Contact JST for details.



# SPADE TONGUE (A type) vinyl-insulated (funnel-entry)



File No.: E42024 LR20812

| Applicable Wire<br>AWG#(mm <sup>2</sup> ) | Stud size |        | Part No.     | Standard | Dimensions mm (in.) |             |              |             |                |               |               | Color  | Tool No.                                     | Qty/box |
|-------------------------------------------|-----------|--------|--------------|----------|---------------------|-------------|--------------|-------------|----------------|---------------|---------------|--------|----------------------------------------------|---------|
|                                           | American  | Metric |              |          | d <sub>2</sub>      | B           | L            | F           | ℓ              | øD            | T             |        |                                              |         |
| 22 to 16<br>(0.25 to 1.65)                | 1-2       | 2      | FVL1.25-2A   |          | 2.2 (.087)          | 4.6 (.181)  | 19.2 (.756)  | 4.3 (.169)  | 9.4<br>(.370)  | 4.2<br>(.165) | 0.8<br>(.031) | Red    | YNT-2216<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | FVL1.25-B3A  |          | 3.2 (.126)          | 5.8 (.228)  | 20.4 (.803)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL1.25-N3A  |          | 3.7 (.146)          | 6.2 (.244)  | 20.4 (.803)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL1.25-YS3A |          | 3.7 (.146)          | 6.4 (.252)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL1.25-S3A  |          | 3.7 (.146)          | 7.2 (.284)  | 20.4 (.803)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL1.25-P3A  |          | 3.7 (.146)          | 7.5 (.295)  | 18.4 (.724)  | 5.5 (.217)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL1.25-YS4A |          | 4.3 (.169)          | 6.4 (.252)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL1.25-S4A  |          | 4.3 (.169)          | 7.2 (.284)  | 20.4 (.803)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL1.25-4A   |          | 4.3 (.169)          | 8.5 (.335)  | 20.4 (.803)  | 7.0 (.276)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL1.25-M5A  |          | 5.3 (.209)          | 8.5 (.335)  | 20.4 (.803)  | 7.0 (.276)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL1.25-5A   |          | 5.3 (.209)          | 9.5 (.374)  | 20.4 (.803)  | 7.0 (.276)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL1.25-S5A  |          | 5.3 (.209)          | 7.2 (.284)  | 20.4 (.803)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 1/4       | 6      | FVL1.25-6A   |          | 6.4 (.252)          | 12.0 (.472) | 26.6 (1.047) | 11.0 (.433) |                |               |               |        |                                              |         |
| 16 to 14<br>(1.04 to 2.63)                | 3-4       | 3      | FVL2-N3A     |          | 3.2 (.126)          | 5.9 (.232)  | 20.4 (.803)  | 6.3 (.248)  | 9.4<br>(.370)  | 4.7<br>(.185) | 0.8<br>(.031) | Blue   | YNT-1614<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000   |
|                                           | 3-4       | 3      | FVL2-M3A     |          | 3.2 (.126)          | 6.0 (.236)  | 19.1 (.752)  | 5.0 (.197)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL2-YS3A    |          | 3.7 (.146)          | 6.4 (.252)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL2-S3A     |          | 3.7 (.146)          | 7.2 (.284)  | 20.6 (.811)  | 6.5 (.256)  |                |               |               |        |                                              |         |
|                                           | 5-6       | 3.5    | FVL2-3A      |          | 3.7 (.146)          | 8.5 (.335)  | 21.4 (.843)  | 7.3 (.287)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL2-YS4A    |          | 4.3 (.169)          | 6.4 (.252)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL2-YM4A    |          | 4.3 (.169)          | 6.8 (.268)  | 20.0 (.787)  | 6.3 (.248)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL2-S4A     |          | 4.3 (.169)          | 7.2 (.284)  | 20.6 (.811)  | 6.5 (.256)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL2-4A      |          | 4.3 (.169)          | 8.5 (.335)  | 21.4 (.843)  | 7.3 (.287)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL2-M5A     |          | 5.3 (.209)          | 8.5 (.335)  | 21.4 (.843)  | 7.3 (.287)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL2-5A      |          | 5.3 (.209)          | 9.5 (.374)  | 21.4 (.843)  | 7.3 (.287)  |                |               |               |        |                                              |         |
|                                           | 1/4       | 6      | FVL2-6A      |          | 6.4 (.252)          | 12.0 (.472) | 26.6 (1.047) | 11.0 (.433) |                |               |               |        |                                              |         |
| 12 to 10<br>(2.63 to 6.64)                | 5-6       | 3.5    | FVL5.5-S3A   |          | 3.7 (.146)          | 7.2 (.284)  | 26.5 (1.043) | 7.5 (.295)  | 13.8<br>(.543) | 7.0<br>(.276) | 1.0<br>(.039) | Yellow | YNT-1210S<br>YA-4<br>BCT-0514                | 500     |
|                                           | 5-6       | 3.5    | FVL5.5-3A    |          | 3.7 (.146)          | 9.5 (.374)  | 26.5 (1.043) | 7.5 (.295)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL5.5-S4A   |          | 4.3 (.169)          | 8.5 (.335)  | 26.5 (1.043) | 7.5 (.295)  |                |               |               |        |                                              |         |
|                                           | 8         | 4      | FVL5.5-4A    |          | 4.3 (.169)          | 9.5 (.374)  | 26.5 (1.043) | 7.5 (.295)  |                |               |               |        |                                              |         |
|                                           | 10        | 5      | FVL5.5-5A    |          | 5.3 (.209)          | 9.5 (.374)  | 26.5 (1.043) | 7.5 (.295)  |                |               |               |        |                                              |         |
|                                           | 1/4       | 6      | FVL5.5-6A    |          | 6.4 (.252)          | 13.5 (.532) | 32.5 (1.280) | 12.2 (.480) |                |               |               |        |                                              |         |
|                                           | 5/16      | 8      | FVL5.5-8A    |          | 8.4 (.331)          | 13.5 (.532) | 32.5 (1.280) | 12.2 (.480) |                |               |               |        |                                              |         |

Note:1) The part numbers indicated in the above table are for products with a brazed seam.




When ordering products with a butted seam, add the prefix "WS" to the part number (ex. FVL2-4A → **FVLWS2-4A**).2) \*The crimping will be more secure if the total cross-sectional area of the wire is at least 0.5 mm<sup>2</sup>.Examples: If the cross-sectional area of the wire is 0.3mm<sup>2</sup>, fold the wire in two when crimping the terminal.If the cross-sectional area of the wire is 0.5mm<sup>2</sup>, crimp the terminal onto the wire as it is.

3) Delivery lead times may vary depending on the product. Contact JST for details.

# Solderless terminals



## SPADE TONGUE (A type) Vinyl-insulated with copper sleeve



File No.: E42024 LR20812

| Applicable Wire<br>AWG#(mm²) | Stud size                  |        | Part No.    |              | Standard   | Dimensions mm (in.) |             |             |             |                                    |               |               |               |        |                                              | Color | Tool No.   | Qty/box        |
|------------------------------|----------------------------|--------|-------------|--------------|------------|---------------------|-------------|-------------|-------------|------------------------------------|---------------|---------------|---------------|--------|----------------------------------------------|-------|------------|----------------|
|                              | American                   | Metric | Straight    | Flared       |            | d <sub>2</sub>      | B           | L           | F           | ℓ                                  | ø D           |               | T             |        |                                              |       |            |                |
|                              |                            |        |             |              |            |                     |             |             |             |                                    | Str.          | Flid.         |               |        |                                              |       |            |                |
| 26 to 22<br>(0.2 to 0.5)     | 3-4                        | 3      | VD0.5-3A    | —            | UL ㉔       | 3.2 (.126)          | 5.0 (.197)  | 16.5 (.650) | 6.0 (.236)  | 8.0<br>(.315)<br><br>8.3<br>(.327) | 2.2<br>(.087) | 2.5<br>(.098) | 0.5<br>(.020) | Yellow | YNT-2622<br>YA-1,YA-2<br>BCT-0514            | 1,000 |            |                |
|                              | 5-6                        | 3.5    | VD0.5-3.7A  | —            | UL ㉔       | 3.7 (.146)          | 6.4 (.252)  | 19.0 (.748) | 7.7 (.303)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 3-4                        | 3      | —           | FVD0.5-3A    | UL ㉔       | 3.2 (.126)          | 5.0 (.197)  | 16.8 (.661) | 6.0 (.236)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | —           | FVD0.5-3.7A  | UL ㉔       | 3.7 (.146)          | 6.4 (.252)  | 19.3 (.760) | 7.7 (.303)  |                                    |               |               |               |        |                                              |       |            |                |
| 22 to 16<br>(0.25 to 1.65)   | 1-2                        | 2      | VD1.25-2A   | FVD1.25-2A   | UL ㉔       | 2.2 (.087)          | 4.6 (.181)  | 19.4 (.764) | 4.3 (.169)  | 9.6<br>(.378)                      | 3.5<br>(.138) | 4.0<br>(.157) | 0.8<br>(.031) | Red    | YNT-2216<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000 |            |                |
|                              | 3-4                        | 3      | VD1.25-B3A  | FVD1.25-B3A  | UL ㉔       | 3.2 (.126)          | 5.8 (.228)  | 20.6 (.811) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD1.25-N3A  | FVD1.25-N3A  | UL ㉔       | 3.7 (.146)          | 6.2 (.244)  | 20.6 (.811) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD1.25-YS3A | FVD1.25-YS3A | UL ㉔       | 3.7 (.146)          | 6.4 (.252)  | 20.2 (.795) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD1.25-S3A  | FVD1.25-S3A  | UL ㉔       | 3.7 (.146)          | 7.2 (.284)  | 20.6 (.811) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD1.25-P3A  | FVD1.25-P3A  | UL ㉔       | 3.7 (.146)          | 7.5 (.295)  | 18.6 (.732) | 5.5 (.217)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD1.25-YS4A | FVD1.25-YS4A | UL ㉔       | 4.3 (.169)          | 6.4 (.252)  | 20.2 (.795) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD1.25-S4A  | FVD1.25-S4A  | UL ㉔       | 4.3 (.169)          | 7.2 (.284)  | 20.6 (.811) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD1.25-4A   | FVD1.25-4A   | UL ㉔       | 4.3 (.169)          | 8.5 (.335)  | 20.6 (.811) | 7.0 (.276)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 10                         | 5      | VD1.25-S5A  | FVD1.25-S5A  | UL ㉔       | 5.3 (.209)          | 7.2 (.284)  | 20.6 (.811) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 10                         | 5      | VD1.25-M5A  | FVD1.25-M5A  | UL ㉔       | 5.3 (.209)          | 8.5 (.335)  | 20.6 (.811) | 7.0 (.276)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 10                         | 5      | VD1.25-5A   | FVD1.25-5A   | UL ㉔       | 5.3 (.209)          | 9.5 (.374)  | 20.6 (.811) | 7.0 (.276)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 1/4                        | 6      | VD1.25-6A   | FVD1.25-6A   | UL ㉔       | 6.4 (.252)          | 12.0 (.472) | 26.8(1.055) | 11.0 (.433) |                                    |               |               |               |        |                                              |       |            |                |
| 16 to 14<br>(1.04 to 2.63)   | 3-4                        | 3      | VD2-N3A     | FVD2-N3A     | UL ㉔       | 3.2 (.126)          | 5.9 (.232)  | 20.6 (.811) | 6.3 (.248)  | 9.6<br>(.378)                      | 4.1<br>(.161) | 4.7<br>(.185) | 0.8<br>(.031) | Blue   | YNT-1614<br>YA-1<br>YA-2<br>YA-4<br>BCT-0514 | 1,000 |            |                |
|                              | 3-4                        | 3      | VD2-M3A     | FVD2-M3A     | UL ㉔       | 3.2 (.126)          | 6.0 (.236)  | 19.3 (.760) | 5.0 (.197)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD2-YS3A    | FVD2-YS3A    | UL ㉔       | 3.7 (.146)          | 6.4 (.252)  | 20.2 (.795) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD2-S3A     | FVD2-S3A     | UL ㉔       | 3.7 (.146)          | 7.2 (.284)  | 20.8 (.819) | 6.5 (.256)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 5-6                        | 3.5    | VD2-3A      | FVD2-3A      | UL ㉔       | 3.7 (.146)          | 8.5 (.335)  | 21.6 (.850) | 7.3 (.287)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD2-YS4A    | FVD2-YS4A    | UL ㉔       | 4.3 (.169)          | 6.4 (.252)  | 20.2 (.795) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD2-YM4A    | FVD2-YM4A    | UL ㉔       | 4.3 (.169)          | 6.8 (.268)  | 20.2 (.795) | 6.3 (.248)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD2-S4A     | FVD2-S4A     | UL ㉔       | 4.3 (.169)          | 7.2 (.284)  | 20.8 (.819) | 6.5 (.256)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 8                          | 4      | VD2-4A      | FVD2-4A      | UL ㉔       | 4.3 (.169)          | 8.5 (.335)  | 21.6 (.850) | 7.3 (.287)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 10                         | 5      | VD2-M5A     | FVD2-M5A     | UL ㉔       | 5.3 (.209)          | 8.5 (.335)  | 21.6 (.850) | 7.3 (.287)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 10                         | 5      | VD2-5A      | FVD2-5A      | UL ㉔       | 5.3 (.209)          | 9.5 (.374)  | 21.6 (.850) | 7.3 (.287)  |                                    |               |               |               |        |                                              |       |            |                |
|                              | 1/4                        | 6      | VD2-6A      | FVD2-6A      | UL ㉔       | 6.4 (.252)          | 12.0 (.472) | 26.8(1.055) | 11.0 (.433) |                                    |               |               |               |        |                                              |       |            |                |
|                              | 12 to 10<br>(2.63 to 6.64) | 5-6    | 3.5         | VD5.5-S3A    | FVD5.5-S3A | UL ㉔                | 3.7 (.146)  | 7.2 (.283)  | 26.7(1.051) |                                    |               |               |               |        |                                              |       | 7.5 (.295) | 14.0<br>(.551) |
| 5-6                          |                            | 3.5    | VD5.5-3A    | FVD5.5-3A    | UL ㉔       | 3.7 (.146)          | 9.5 (.374)  | 26.7(1.051) | 7.5 (.295)  |                                    |               |               |               |        |                                              |       |            |                |
| 8                            |                            | 4      | VD5.5-S4A   | FVD5.5-S4A   | UL ㉔       | 4.3 (.169)          | 8.5 (.335)  | 26.7(1.051) | 7.5 (.295)  |                                    |               |               |               |        |                                              |       |            |                |
| 8                            |                            | 4      | VD5.5-4A    | FVD5.5-4A    | UL ㉔       | 4.3 (.169)          | 9.5 (.374)  | 26.7(1.051) | 7.5 (.295)  |                                    |               |               |               |        |                                              |       |            |                |
| 10                           |                            | 5      | VD5.5-5A    | FVD5.5-5A    | UL ㉔       | 5.3 (.209)          | 9.5 (.374)  | 26.7(1.051) | 7.5 (.295)  |                                    |               |               |               |        |                                              |       |            |                |
| 1/4                          |                            | 6      | VD5.5-6A    | FVD5.5-6A    | UL ㉔       | 6.4 (.252)          | 13.5 (.532) | 32.7(1.287) | 12.2 (.480) |                                    |               |               |               |        |                                              |       |            |                |
| 5/16                         |                            | 8      | VD5.5-8A    | FVD5.5-8A    | UL ㉔       | 8.4 (.331)          | 13.5 (.532) | 32.7(1.287) | 12.2 (.480) |                                    |               |               |               |        |                                              |       |            |                |

Note:1) The part numbers indicated in the above table are for products with a brazed seam.

When ordering products with a butted seam, add the prefix "WS" to the part number (ex. VD2-4A →VDWS2-4A).

2) To order products with nylon insulation, change the "V" in the part number prefix to "N" (ex. VD2-4A →ND2-4A).

Because nylon absorbs moisture, care must be taken concerning storage.

3) Delivery lead times may vary depending on the product. Contact JST for details.