





- NOTES:
1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP), GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
 2. FINISH: 30μN MIN GOLD IN CONTACT AREA, SELECTIVE TIN OR
SELECTIVE TIN-LEAD ON PCB TAILS, NICKEL OVERALL.
 3. REFER TO MOLEX PRODUCT SPEC PS-76060-999 FOR PERFORMANCE SPECIFICATIONS
AND ADDITIONAL PCB INFORMATION.
 4. EACH SIGNAL WAFER CONTAINS 2 COLUMNS OF TERMINALS.
 5. PRODUCT IS PACKAGED PER PK-70873-589.
 6. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
 7. REFER TO MOLEX SALES DRAWING SD-76145-002 FOR THE MATING HEADERS AND
SD-76560-002 FOR THE MATING RAM CONNECTORS.
 8. REFER TO MOLEX ROUTING GUIDE AS-76060-990 FOR ANTIPAD AND ROUTING
RECOMMENDATIONS.
 9. PART NUMBER 76150-3020 SHOWN ON DRAWING. KEYING FEATURES WILL CHANGE
WITH COLUMN SIZE.
 10. MINIMUM BOARD THICKNESS IS 1.00 mm FOR COMPLIANT PIN FUNCTIONALITY.
 11. WHEN USING MOLEX SUPPLIED #2-32 SCREW 73726-0000 (9.50mm ±0.38
THREADABLE SCREW LENGTH), THE MAXIMUM BOARD THICKNESS IS 4.4mm.



DAUGHTERCARD HOLE PATTERN
(CONNECTOR SIDE)

ENHANCED PEG UPDATE EC NO: UCP2014-4723 DRAWN BY MILLER 2014/05/06 CHKD: APPR: TELLO 2014/05/13	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY JLAURX	DATE 2008/03/12	TITLE IMPACT 100 OHM DC 6 PAIR SIGNAL MODULE GUIDE LEFT SALES DWG		
			4 PLACES	± ---	± ---	CHECKED BY TELO	DATE 2008/03/12			
			3 PLACES	± ---	± ---	APPROVED BY JLAURX	DATE 2010/11/04			
			2 PLACES	± 0.13	± ---	MATERIAL NO.		DOCUMENT NO.	SHEET NO. 1 OF 2	
			1 PLACE	± 0.25	± ---	SEE CHART		SD-76150-002		
			ANGULAR ±1/2°			MOLEX INCORPORATED				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A" MAX	DIM "B"	PTHØ
76150-**-10	10	60	26.60	17.10	0,46 ±0,05
76150-**-14	14	84	34.20	24.70	
76150-**-16	16	96	38.00	28.50	
76150-**-20	10	60	26.60	17.10	0,39 ±0,05
76150-**-24	14	84	34.20	24.70	
76150-**-26	16	96	38.00	28.50	

76150-****

3 = LEFT GUIDED LEAD-FREE

POLARIZATION KEY ORIENTATION

0 = NO KEY

1 = A

2 = B

3 = C

4 = D

5 = E

6 = F

7 = G

8 = H

OF COLUMNS

10 = 10 COL 0.46 PTH

14 = 14 COL 0.46 PTH

16 = 16 COL 0.46 PTH

20 = 10 COL 0.39 PTH

24 = 14 COL 0.39 PTH

26 = 16 COL 0.39 PTH

SEE SHEET 1 EC NO: UCP2014-4723 DRWN:8 MILLER 2014/05/06 CHKD: APPR:TELO 2014/05/13	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY JLAURX	DATE 2008/03/12	TITLE IMPACT 100 OHM DC 6 PAIR SIGNAL MODULE GUIDE LEFT SALES DWG			
			4 PLACES	±	---	±	---			CHECKED BY TELO	
			3 PLACES	±	---	±	---	APPROVED BY JLAURX		DATE 2010/11/04	
			2 PLACES	±	0.13	±	---				
			1 PLACE	±	0.25	±	---	MATERIAL NO. SD-76150-002			
			0 PLACE	±		±					
			ANGULAR ±1/2°				DOCUMENT NO. 2 OF 2			SHEET NO. 2 OF 2	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								