


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	90 (400.3)	EXTRA HEAVY	1.3 (590)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	90 (400.3)	EXTRA HEAVY	2.5 (1134)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	90 (400.3)	EXTRA HEAVY	2.8 (1270)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	90 (400.3)	EXTRA HEAVY	3.8 (1724)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

W10001BH/06-SS-15129

										CAD FILENAME/LAYERS	
										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										PAN-TY RELEASABLE LASHING TIES - POLYPROPYLENE	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX) ± .010(.25) (.XX) ± .02(.5) ANGLES ± -----	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
---	----	---		CHANGED NOTE 1 "SEE CURRENT PRICE SHEET...", TO "SEE www.panduit.com..."	----	---				DRAWN BY DWR	MAT'L: POLYPROPYLENE
6	9/26/08	JABO		CORRECTED 'F' METRIC CONVERSION OF PRT5EH, WAS (.510), NOW (.511)	SS-15129	6				DATE 7-15-77	DWG SS-15129 A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D HVP	SIZE