





LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			AJ2	REVISED PER ECO-11-004587			11MAR11	RK	HMR




△6




1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
 2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
 3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
- △4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- △5 CIRCUIT NUMBER 1 LOCATION.
- △6 DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- △7 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- △8 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- △9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




DETAIL A
OPTIONAL CONSTRUCTIONS



27.43±0.38



RECOMMENDED PANEL CUT OUT



3-DIMENSIONAL MODEL
NTS

6.99	.275	33.40	1.315
4.45	.175	33.02	1.300
2.79	.110	27.43	1.080
2.54	.100	26.16	1.030
2.29	.090	25.91	1.020
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.89	.350
0.13	.005	8.13	.320
MM	IN	MM	IN

CONVERSION TABLE

△9 OBSOLETE	BLACK	1-480711-9
	GRAY	1-480711-8
	BLUE	1-480711-6
	GREEN	1-480711-5
	YELLOW	1-480711-4
	ORANGE	1-480711-3
	RED	1-480711-2
	BROWN	1-480711-1
	NATURAL	1-480711-0
COLOR		PART NO






△9 SUPERSEDED BY 1-480711-0

△9 SUPERSEDED BY 1-480711-0


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 29JUL2004	 TE Connectivity	
DIMENSIONS: mm		CHK S. RIDGILL 29JUL2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 29JUL2004	NAME	

LOC	DIST	REVISIONS				
		REV	DATE	DESCRIPTION	BY	APP
CM	00	-	-	SEE SHEET 1	-	-

- 1 . STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE);CLARIFICATION MARKS UNDER THE 6 & 9.
2. CHARACTERS TO BE STAMPED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.
3. VIOLET,BLACK,BROWN,AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



5.08	.200	-	-
4.70	.185	33.02	1.300
3.18	.125	27.43	1.080
0.38	.015	25.91	1.020
0.25	.010	20.32	.800
0.13	.005	8.13	.320
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	29JUL2004	 TE Connectivity										
		CHK S. RIDGILL	29JUL2004											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV S. RIDGILL	29JUL2004	NAME	CAP, 15 CIRCUIT, UNIVERSAL MATE-N-LOK TM							
		0 PLC	± -	PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
		1 PLC	± -											
		2 PLC	± 0.13											
		3 PLC	± -											
ANGLES		4 PLC	± 0°30'	APPLICATION SPEC										
FINISH		-		WEIGHT		-	A1		-					
MATERIAL NYLON. UL94V-2				CUSTOMER DRAWING										
						SCALE		4:1	SHEET	2	OF	2	REV	A1