





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

(C) COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.



P/N 293054-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS: TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

mm	0 PLC	±-
1 PLC	±0.3	
2 PLC	±-	
3 PLC	±-	
4 PLC ANGLES	±-	±1

MATERIAL PA66 GF25  
UL 94 VODWN U.AIME 04MAY2006  
CHK U.AIME 04MAY2006

APVD G.TURCO 04MAY2006

PRODUCT SPEC 108-20268

APPLICATION SPEC

- -

WEIGHT -

- -

CUSTOMER DRAWING

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
0		-FIRST ISSUE	04MAY2006	UA	GT
B		ECR-10-021916	25OCT2010	UA	GT

## NOTES:

- 1) TE P/N
- 2) RAW MAT'L CODE
- 3) DATE CODE
- 4) MOULD CAVITY IDENTIFICATION
- 5) TE NECTOR TRADEMARK
- 6) WIRE SIZE INDICATION
  - MIN.: 1.5 sqmm
  - MAX.: 2.5 sqmm

7) CABLES TO BE USED:  
MIN. INSULATION DIA.: 8.3 mm (WIRE SIZE 1.5sqmm)  
MAX. INSULATION DIA.: 10.2 mm (WIRE SIZE 2.5sqmm)

8) PACKAGING ACCORDING TO TYCO SPEC 107-20252

9) TO BE USED ON FREE-HANGING VERSION

- SPRING CLAMP VERSION  
(SEE TE C-DWGS 293046, 293045)
- SCREW VERSION  
(SEE TE C-DWGS 293049, 293047)
- CRIMP VERSION  
(SEE TE C-DWGS 293052, 293051)

10) OPTIONAL SCREWS M3x12 (NOT INCLUDED)  
ACCORDING TO "UNI9709", OR "UNI 9707",  
OR "UNI10227", OR "UNI10228"

293054-2	WHITE	B
293054-1	BLACK	B
TYCO P/N	COLOUR	REV.

Tyco Electronics AMP Italia S.p.A.  
C.so F.lli Cervi 15 Collegno (TO)

TYCO NECTOR\* HERMAPHRODITE  
HALF SHELL FOR 3 POS. CONN.S

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 300779	C-293054		-

SCALE 5:1 SHEET 1 OF 1 REV B