


# Hermetically Sealed High Precision Bulk Metal® Foil Technology Aerospace Resistors with TCR of $\pm 1 \text{ ppm}/^\circ\text{C}$ , Tolerance to $\pm 0.005 \%$ and Load Life Stability of $\pm 0.005 \%$



## Any value at any tolerance available within resistance range

The "VH" series of resistors is the hermetic version of several molded "S" series devices. Hermetic sealing eliminates the ingress of both oxygen, which degrades resistors over long periods, and moisture which degrades resistors more quickly. These parts are made with glass to metal seal enclosures employing Kovar eyelets which allow the copper leads to pass through the enclosure to minimize the thermal EMF from the lead junctions. Rubber fill between the metal housing and resistance element acts both as a mechanical damper and thermal transfer path.

VHS102 and VH102K are the hermetically-sealed counterpart of the S102C and S102K high-performance molded resistors. VHS555 is the hermetically-sealed version of the S555, MIL style RNC90Y.

## FEATURES

- Temperature coefficient of resistance (TCR):  
-  $-55^\circ\text{C}$  to  $+125^\circ\text{C}$ ,  $+25^\circ\text{C}$  ref.:  
VH102K:  $\pm 1 \text{ ppm}/^\circ\text{C}$  typical  
VHS102:  $\pm 2 \text{ ppm}/^\circ\text{C}$  typical  
VHS555:  $\pm 5 \text{ ppm}/^\circ\text{C}$  maximum
- Tolerance: to  $\pm 0.005 \%$
- Resistance range:  $1 \Omega$  to  $150 \text{ k}\Omega$  (higher or lower resistance values are available)
- Load life stability:  $0.005 \%$  ( $70^\circ\text{C}$  for 2000 h at rated power)
- Electrostatic discharge (ESD)  $> 25 \text{ kV}$
- Power rating:  $0.6 \text{ W}$  at  $+70^\circ\text{C}$ ;  $0.3 \text{ W}$  at  $+125^\circ\text{C}$
- Non inductive, non capacitive design
- Non hot spot design
- Rise time:  $1.0 \text{ ns}$  without ringing
- Current Noise:  $< -40 \text{ dB}$
- Thermal EMF:  $0.05 \mu\text{V}/^\circ\text{C}$  typical
- Voltage coefficient:  $< 0.1 \text{ ppm/V}$
- Non inductive:  $< 0.08 \mu\text{H}$
- Termal finishes available: lead (Pb)-free tin/lead alloy
- Impervious to harmful environments - oil filled
- For better performance, please see VH102Z datasheet



**RoHS\***  
COMPLIANT

**TABLE 1 - MODEL SELECTION**

| MODEL NUMBER | RESISTANCE RANGE<br>( $\Omega$ )                    | STANDARD RESISTANCE TOLERANCE <sup>1)</sup> % |                                  | MAXIMUM WORKING VOLTAGE <sup>2)</sup> | AMBIENT POWER RATING <sup>3)</sup> ††† |             | AVERAGE WEIGHT (g) | DIMENSIONS                    |                                                                                                                  |                                                                                              |
|--------------|-----------------------------------------------------|-----------------------------------------------|----------------------------------|---------------------------------------|----------------------------------------|-------------|--------------------|-------------------------------|------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|
|              |                                                     | TIGHTEST                                      | LOOSEST                          |                                       | at + 70 °C                             | at + 125 °C |                    |                               | INCHES                                                                                                           | mm                                                                                           |
| VH102K†      | 30.1 to 150K                                        | ± 0.005                                       | ± 1.0                            | 300                                   | 0.6 W                                  | 0.3 W       | 1.4                | W<br>L<br>H<br>LL<br>LS<br>ST | 0.185 maximum<br>0.435 maximum<br>0.430 maximum††††<br>1 ± 0.125<br>0.150 ± 0.010 <sup>4)</sup><br>0.095 maximum | 4.70 maximum<br>11.05 maximum<br>10.92 maximum<br>25.4 ± 3.18<br>3.81 ± 0.25<br>2.41 maximum |
| VHS102       | 20 to < 30.1<br>10 to < 20<br>5 to < 10<br>1 to < 5 | ± 0.01<br>± 0.05<br>± 0.10<br>± 0.25          | ± 1.0<br>± 1.0<br>± 1.0<br>± 1.0 |                                       |                                        |             |                    |                               |                                                                                                                  |                                                                                              |
| VHS555††     | 30.1 to 150K                                        | ± 0.005                                       | ± 1.0                            |                                       |                                        |             |                    |                               |                                                                                                                  |                                                                                              |
|              | 16.2 to < 30.1<br>4.99 to < 16.2<br>1 to < 4.99     | ± 0.05<br>± 0.10<br>± 0.25                    | ± 1.0<br>± 1.0<br>± 1.0          |                                       |                                        |             |                    |                               |                                                                                                                  |                                                                                              |

## Notes


† Available from  $1 \Omega$  to  $100 \text{ k}\Omega$  only

†† Contains RNC90Y inside ( $4.99 \Omega$  to  $121 \text{ k}\Omega$ )

††† Above  $100 \text{ k}\Omega$  VHS102 power is derated to  $0.4 \text{ W}$  at  $+70^\circ\text{C}$  and  $0.2 \text{ W}$  at  $+125^\circ\text{C}$

††††  $0.375 \text{ H}$  available

**FIGURE 1 - STANDARD IMPRINTING AND DIMENSIONS**



\* Pb containing terminations are not RoHS compliant, exemptions may apply

**TABLE 2 - TOLERANCE AND TCR VS. RESISTANCE VALUE**

| RESISTOR | RESISTANCE VALUE ( $\Omega$ ) | TYPICAL TCR AND MAXIMUM SPREAD<br>(- 55 °C to + 125 °C, + 25 °C ref.)<br>(ppm/°C) |
|----------|-------------------------------|-----------------------------------------------------------------------------------|
| VHS102   | 80 to 150K                    | $\pm 2 \pm 2.5$                                                                   |
| VH102K   | 80 to 100K                    | $\pm 1 \pm 2.5$                                                                   |
| VHS102   | 50 to < 80                    | $\pm 2 \pm 3.5$                                                                   |
| VH102K   |                               | $\pm 1 \pm 3.5$                                                                   |
| VHS102   | 1 to < 50                     | $\pm 2 \pm 4.5$                                                                   |
| VH102K   |                               | $\pm 1 \pm 4.5$                                                                   |


**TABLE 3 - SPECIFICATIONS<sup>5)</sup>**

|                                                   |                                                           |                                  |                                                     |                                       |
|---------------------------------------------------|-----------------------------------------------------------|----------------------------------|-----------------------------------------------------|---------------------------------------|
| Selected <sup>6)</sup> TCR Tracking <sup>8)</sup> | 0.5 ppm/°C                                                |                                  |                                                     |                                       |
| Stability <sup>12)</sup>                          |                                                           |                                  |                                                     |                                       |
| Load life at 2000 h                               | VH102K<br>± 0.025 %<br>± 0.005 %                          | VHS102<br>± 0.025 %<br>± 0.005 % | VHS555<br>± 0.015 %<br>± 0.0025 %                   | at 0.3 W/+ 125 °C<br>at 0.1 W/+ 60 °C |
| Load life at 10 000 h                             | ± 0.02 %                                                  | ± 0.02 %                         | ± 0.01 %                                            | at 0.05 W/+ 125 °C                    |
| Shelf Life Stability                              | ± 5 ppm<br>± 10 ppm                                       | (0.0005 %)<br>(0.001 %)          | maximum ΔR after 1 year<br>maximum ΔR after 3 years |                                       |
| Current Noise                                     | < 0.010 μV <sub>RMS</sub> /V of applied voltage (- 40 dB) |                                  |                                                     |                                       |
| High Frequency Operation                          |                                                           |                                  |                                                     |                                       |
| Rise time                                         | 1.0 ns                                                    |                                  |                                                     |                                       |
| Inductance (L) <sup>9)</sup>                      | 0.1 μH maximum; 0.08 μH typical                           |                                  |                                                     |                                       |
| Capacitance (C)                                   | 1.0 pF maximum; 0.5 pF typical                            |                                  |                                                     |                                       |
| Voltage Coefficient                               | < 0.1 ppm/V <sup>10)</sup>                                |                                  |                                                     |                                       |
| Thermal EMF <sup>11)</sup>                        | 0.1 μV/°C maximum; 0.05 μV/°C typical 1 μV/W              |                                  |                                                     |                                       |
| Hermeticity                                       | 10 <sup>-7</sup> atmospheric cc/s maximum                 |                                  |                                                     |                                       |


**Notes:**

- Standard resistance tolerance:  $\pm 0.005 \%$ ;  $\pm 0.01 \%$ ;  $\pm 0.02 \%$ ;  $\pm 0.05 \%$ ;  $\pm 0.1 \%$ ;  $\pm 0.25 \%$ ;  $\pm 0.5 \%$ ;  $\pm 1.0 \%$ .
- Not to exceed power rating of resistor.
- See Figure 2 below.
- 0.200" (5.08 mm) lead spacing available (except VHS555) - specify VH102J (S102C type), VH102L (S102K type).
- Maximum is 1.0 % A.Q.L. standard for all specifications except TCR. (For TCR information see notes 6 to 10.) Typical is a designers reference which represents that 85 % of the units supplied, over a long period of time, will be at least the figure shown or better.
- Vishay maximum TCR spread is defined as the 3  $\sigma$  (sigma) limit of a normal Gaussian distribution (99.73 % of a production lot) which is within a band, centered on the nominal curve. This Vishay maximum TCR spread is no greater than  $\pm 2.5$  ppm/°C from nominal throughout the full temperature range. This definition of the Vishay maximum TCR spread from nominal applies to all resistance values. However, as the resistance value decreases below 80  $\Omega$ , the Vishay maximum TCR spread from nominal specification starts to increase. (See Figure 3 in datasheet "7 Technical Reasons to Specify Vishay Bulk Metal® Foil Resistive Components")
- Selected TCR tracking is available for specially ordered lots of resistors. The selected TCR tracking can be 3, 2, 1 and as close as 0.5 ppm/°C throughout the full temperature range.
- TCR tracking is a measure of the similarity of resistance value change in two or more resistors which are undergoing the same temperature changes. Tracking could be expressed as the difference in the temperature coefficients of the resistors, expressed in ppm/°C as  $(\Delta R_1/R_1 \text{ to } \Delta R_2/R_2) \times 10^{-6}/\Delta T^\circ C$ . When a number of resistors are referenced to a nominal TCR, the spread or envelope around the nominal would be the difference. If the spread is  $\pm 1.5$  ppm/°C about a nominal, the tracking, as defined above, will be 3 ppm/°C.
- Inductance (L) due mainly to the leads.
- The resolution limit of existing test equipment (within the measurement capability of the equipment, or "essentially zero")
- $\mu V/^\circ C$  relates to EMF due to lead temperature difference and  $\mu V/W$  due to power applied to the resistor.
- Load life  $\Delta R$  maximum can be reduced through in-house oriented processes.

**FIGURE 2 - TRIMMING TO VALUES**  
(Conceptual Illustration)



**FIGURE 3 - POWER DERATING CURVE**



**TABLE 4 - ENVIRONMENTAL PERFORMANCE COMPARISON**


|                                        | MIL-PRF-55182/9<br>CHARACTERISTIC Y MAXIMUM $\Delta R$ | VH102K<br>TYPICAL <sup>5)</sup> $\Delta R$ | VHS102<br>TYPICAL <sup>5)</sup> $\Delta R$             | VHS555<br>TYPICAL <sup>5)</sup> $\Delta R$ |
|----------------------------------------|--------------------------------------------------------|--------------------------------------------|--------------------------------------------------------|--------------------------------------------|
| <b>Test Group I</b>                    |                                                        |                                            |                                                        |                                            |
| Thermal shock                          | $\pm 0.05\%$                                           | $\pm 0.002\%$                              | $\pm 0.002\%$                                          | $\pm 0.002\%$                              |
| Overload                               | $\pm 0.05\%$                                           | $\pm 0.003\%$                              | $\pm 0.003\%$                                          | $\pm 0.003\%$                              |
| <b>Test Group II</b>                   |                                                        |                                            |                                                        |                                            |
| Resistance temperature characteristics | $\pm 5 \text{ ppm}/^\circ\text{C}$                     | See Figures 7 and 8 <sup>1)</sup>          | See Figures 1 and 2, and Figures 5 and 6 <sup>1)</sup> |                                            |
| Temperature storage                    | $\pm 0.05\%$                                           | $\pm 0.005\%$                              | $\pm 0.005\%$                                          | $\pm 0.0025$                               |
| Low temperature operation              | $\pm 0.05\%$                                           | $\pm 0.005\%$                              | $\pm 0.005\%$                                          | $\pm 0.005\%$                              |
| Terminal strength                      | $\pm 0.02\%$                                           | $\pm 0.002\%$                              | $\pm 0.002\%$                                          | $\pm 0.002\%$                              |
| <b>Test Group III</b>                  |                                                        |                                            |                                                        |                                            |
| DWV                                    | $\pm 0.02\%$                                           | $\pm 0.005\%$                              | $\pm 0.005\%$                                          | $\pm 0.002\%$                              |
| Insulation resistance                  | $10^4 \text{ M}\Omega$                                 | $40 \times 10^5 \text{ M}\Omega$           | $40 \times 10^5 \text{ M}\Omega$                       | $40 \times 10^5 \text{ M}\Omega$           |
| Resistance to solder heat              | $\pm 0.02\%$                                           | $\pm 0.002\%$                              | $\pm 0.002\%$                                          | $\pm 0.002\%$                              |
| Moisture resistance                    | $\pm 0.05\%$                                           | $\pm 0.005\%$                              | $\pm 0.005\%$                                          | $\pm 0.005\%$                              |
| <b>Test Group IV</b>                   |                                                        |                                            |                                                        |                                            |
| Shock                                  | $\pm 0.01\%$                                           | $\pm 0.002\%$                              | $\pm 0.002\%$                                          | $\pm 0.002\%$                              |
| Vibration                              | $\pm 0.02\%$                                           | $\pm 0.002\%$                              | $\pm 0.002\%$                                          | $\pm 0.002\%$                              |
| <b>Test Group V</b>                    |                                                        |                                            |                                                        |                                            |
| Life test at 0.3 W/+ 125 °C            |                                                        |                                            |                                                        |                                            |
| 2000 h                                 | $\pm 0.05\%$                                           | $\pm 0.03\%$                               | $\pm 0.03\%$                                           | $\pm 0.01\%$                               |
| 10 000 h                               | $\pm 0.5\%$                                            | $\pm 0.05\%$                               | $\pm 0.05\%$                                           | $\pm 0.02\%$                               |
| <b>Test Group Va</b>                   |                                                        |                                            |                                                        |                                            |
| + 70 °C power rating                   | $\pm 0.05\%$                                           | $\pm 0.02\%$                               | $\pm 0.02\%$                                           | $\pm 0.02\%$                               |
| <b>Test Group VI</b>                   |                                                        |                                            |                                                        |                                            |
| High temperature exposure              | $\pm 0.05\%$                                           | $\pm 0.05\%$                               | $\pm 0.05\%$                                           | $\pm 0.04\%$                               |
| <b>Test Group VII</b>                  |                                                        |                                            |                                                        |                                            |
| Voltage coefficient                    | 0.0005 %/V                                             | < 0.00001 %/V                              | < 0.00001 %/V                                          | < 0.00001 %/V                              |

**Notes:**

- These figures can be found in data sheet "7 Technical Reasons to Specify Bulk Metal® Foil Resistive Components."
- See previous page for numbered footnotes.

### TABLE 5 - GLOBAL PART NUMBER INFORMATION

NEW GLOBAL PART NUMBER: Y578780K5000V9L (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y5787 80K5000 V 9 L:

TYPE: VH102K


VALUE: 80.5  $k\Omega$

ABSOLUTE TOLERANCE:  $\pm 0.005\%$

TERMINATION: lead (Pb)-free

PACKAGING: bulk pack

HISTORICAL PART NUMBER: VH102KT 8K500 V B (will continue to be used)



#### Note

\* Application engineering release: for non-standard requests, please contact application engineering.

## Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

**To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at [vpgsensors.com](http://vpgsensors.com).

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.