


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 150 uF, +/-20% Tol, 16 V, Lead Spacing=6.35 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	10.20	
H	18.60	
F	0.50	+/-0.05
S	6.35	+/-0.38
LL	4.75	+/-0.81

General Information	
Supplier:	KEMET
Application:	General Purpose
Part Type Description:	General Purpose Radial Conformal (Dipped)
Body Type:	Radial Conformal (Dipped)
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	150 uF
Tolerance:	+/-20%
Voltage:	16 V (85C)
Voltage:	12 V (125C Surge)
Voltage:	0.16 V (125C Reverse)
Temperature Range:	-55/+125C
Leakage Current:	4.3 uA
Dissipation Factor:	8%

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.