

## DM74LS157/DM74LS158 Quad 2-Line to 1-Line Data Selectors/Multiplexers

### General Description

These data selectors/multiplexers contain inverters and drivers to supply full on-chip data selection to the four output gates. A separate strobe input is provided. A 4-bit word is selected from one of two sources and is routed to the four outputs. The LS157 presents true data whereas the LS158 presents inverted data to minimize propagation delay time.

### Applications



- Expand any data input point
- Multiplex dual data buses
- Generate four functions of two variables (one variable is common)

- Source programmable counters

### Features

- Buffered inputs and outputs
- Typical Propagation Time  
LS157 9 ns  
LS158 7 ns
- Typical Power Dissipation  
LS157 49 mW  
LS158 24 mW

### Connection Diagrams



### Function Table

| Inputs |        |   |   | Output Y |       |
|--------|--------|---|---|----------|-------|
| Strobe | Select | A | B | LS157    | LS158 |
| H      | X      | X | X | L        | H     |
| L      | L      | L | X | L        | H     |
| L      | L      | H | X | H        | L     |
| L      | H      | X | L | L        | H     |
| L      | H      | X | H | H        | L     |

H = High Level, L = Low Level, X = Don't Care

**Absolute Maximum Ratings** (Note 1)

Supply Voltage  
Input Voltage  
Operating Free Air Temperature Range

7V  
7V

DM54LS and 54LS  
DM74LS  
Storage Temperature Range

–55°C to +125°C  
0°C to +70°C  
–65°C to +150°C

**Recommended Operating Conditions**

| Symbol   | Parameter                      | DM54LS157 |     |      | DM74LS157 |     |      | Units |
|----------|--------------------------------|-----------|-----|------|-----------|-----|------|-------|
|          |                                | Min       | Nom | Max  | Min       | Nom | Max  |       |
| $V_{CC}$ | Supply Voltage                 | 4.5       | 5   | 5.5  | 4.75      | 5   | 5.25 | V     |
| $V_{IH}$ | High Level Input Voltage       | 2         |     |      | 2         |     |      | V     |
| $V_{IL}$ | Low Level Input Voltage        |           |     | 0.7  |           |     | 0.8  | V     |
| $I_{OH}$ | High Level Output Current      |           |     | –0.4 |           |     | –0.4 | mA    |
| $I_{OL}$ | Low Level Output Current       |           |     | 4    |           |     | 8    | mA    |
| $T_A$    | Free Air Operating Temperature | –55       |     | 125  | 0         |     | 70   | °C    |

**Note 1:** The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

**'LS157 Electrical Characteristics**

over recommended operating free air temperature range (unless otherwise noted)

| Symbol   | Parameter                         | Conditions                                      | Min    | Typ<br>(Note 2) | Max  | Units         |
|----------|-----------------------------------|-------------------------------------------------|--------|-----------------|------|---------------|
| $V_I$    | Input Clamp Voltage               | $V_{CC} = \text{Min}$ , $I_I = -18 \text{ mA}$  |        |                 | –1.5 | V             |
| $V_{OH}$ | High Level Output Voltage         | $V_{CC} = \text{Min}$ , $I_{OH} = \text{Max}$   | DM54   | 2.5             | 3.4  | V             |
|          |                                   | $V_{IL} = \text{Max}$ , $V_{IH} = \text{Min}$   | DM74   | 2.7             | 3.4  |               |
| $V_{OL}$ | Low Level Output Voltage          | $V_{CC} = \text{Min}$ , $I_{OL} = \text{Max}$   | DM54   |                 | 0.25 | V             |
|          |                                   | $V_{IL} = \text{Max}$ , $V_{IH} = \text{Min}$   | DM74   |                 | 0.35 |               |
|          |                                   | $I_{OL} = 4 \text{ mA}$ , $V_{CC} = \text{Min}$ | DM74   |                 | 0.25 |               |
| $I_I$    | Input Current @ Max Input Voltage | $V_{CC} = \text{Max}$                           | S or G |                 | 0.2  | mA            |
|          |                                   | $V_I = 7 \text{ V}$                             | A or B |                 | 0.1  |               |
| $I_{IH}$ | High Level Input Current          | $V_{CC} = \text{Max}$                           | S or G |                 | 40   | $\mu\text{A}$ |
|          |                                   | $V_I = 2.7 \text{ V}$                           | A or B |                 | 20   |               |
| $I_{IL}$ | Low Level Input Current           | $V_{CC} = \text{Max}$                           | S or G |                 | –0.8 | mA            |
|          |                                   | $V_I = 0.4 \text{ V}$                           | A or B |                 | –0.4 |               |
| $I_{OS}$ | Short Circuit Output Current      | $V_{CC} = \text{Max}$                           | DM54   | –20             | –100 | mA            |
|          |                                   | (Note 3)                                        | DM74   | –20             | –100 |               |
| $I_{CC}$ | Supply Current                    | $V_{CC} = \text{Max}$ (Note 4)                  |        | 9.7             | 16   | mA            |

**Note 2:** All typicals are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^\circ\text{C}$ .

**Note 3:** Not more than one output should be shorted at a time, and the duration should not exceed one second.

**Note 4:**  $I_{CC}$  is measured with 4.5V applied to all inputs and all outputs open.

**'LS157 Switching Characteristics**

at  $V_{CC} = 5 \text{ V}$  and  $T_A = 25^\circ\text{C}$

| Symbol           | Parameter                                          | From (Input)<br>To (Output) | R <sub>L</sub> = 2 kΩ  |     |                        |     | Units |
|------------------|----------------------------------------------------|-----------------------------|------------------------|-----|------------------------|-----|-------|
|                  |                                                    |                             | C <sub>L</sub> = 15 pF |     | C <sub>L</sub> = 50 pF |     |       |
|                  |                                                    |                             | Min                    | Max | Min                    | Max |       |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Data<br>to Y                |                        | 14  |                        | 18  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Data<br>to Y                |                        | 14  |                        | 23  | ns    |

### 'LS157 Switching Characteristics (Continued)

at  $V_{CC} = 5V$  and  $T_A = 25^\circ C$

| Symbol           | Parameter                                          | From (Input)<br>To (Output) | R <sub>L</sub> = 2 kΩ  |     |                        |     | Units |
|------------------|----------------------------------------------------|-----------------------------|------------------------|-----|------------------------|-----|-------|
|                  |                                                    |                             | C <sub>L</sub> = 15 pF |     | C <sub>L</sub> = 50 pF |     |       |
|                  |                                                    |                             | Min                    | Max | Min                    | Max |       |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Strobe<br>to Y              |                        | 20  |                        | 24  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Strobe<br>to Y              |                        | 21  |                        | 30  | ns    |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Select<br>to Y              |                        | 23  |                        | 28  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Select<br>to Y              |                        | 27  |                        | 32  | ns    |

### Recommended Operating Conditions

| Symbol   | Parameter                      | DM54LS158 |     |      | DM74LS158 |     |      | Units      |
|----------|--------------------------------|-----------|-----|------|-----------|-----|------|------------|
|          |                                | Min       | Nom | Max  | Min       | Nom | Max  |            |
| $V_{CC}$ | Supply Voltage                 | 4.5       | 5   | 5.5  | 4.75      | 5   | 5.25 | V          |
| $V_{IH}$ | High Level Input Voltage       | 2         |     |      | 2         |     |      | V          |
| $V_{IL}$ | Low Level Input Voltage        |           |     | 0.7  |           |     | 0.8  | V          |
| $I_{OH}$ | High Level Output Current      |           |     | -0.4 |           |     | -0.4 | mA         |
| $I_{OL}$ | Low Level Output Current       |           |     | 4    |           |     | 8    | mA         |
| $T_A$    | Free Air Operating Temperature | -55       |     | 125  | 0         |     | 70   | $^\circ C$ |

### 'LS158 Electrical Characteristics

over recommended operating free air temperature range (unless otherwise noted)

| Symbol   | Parameter                            | Conditions                                                                               | Min              | Typ<br>(Note 5) | Max          | Units   |
|----------|--------------------------------------|------------------------------------------------------------------------------------------|------------------|-----------------|--------------|---------|
| $V_I$    | Input Clamp Voltage                  | $V_{CC} = \text{Min}, I_I = -18\text{ mA}$                                               |                  |                 | -1.5         | V       |
| $V_{OH}$ | High Level Output<br>Voltage         | $V_{CC} = \text{Min}, I_{OH} = \text{Max}$<br>$V_{IL} = \text{Max}, V_{IH} = \text{Min}$ | DM54<br>2.5      | 3.4             |              | V       |
|          |                                      |                                                                                          | DM74<br>2.7      | 3.4             |              |         |
| $V_{OL}$ | Low Level Output<br>Voltage          | $V_{CC} = \text{Min}, I_{OL} = \text{Max}$<br>$V_{IL} = \text{Max}, V_{IH} = \text{Min}$ | DM54             | 0.25            | 0.4          | V       |
|          |                                      |                                                                                          | DM74             | 0.35            | 0.5          |         |
|          |                                      | $I_{OL} = 4\text{ mA}, V_{CC} = \text{Min}$                                              | DM74             | 0.25            | 0.4          |         |
| $I_I$    | Input Current @ Max<br>Input Voltage | $V_{CC} = \text{Max}$<br>$V_I = 7V$                                                      | S or G<br>A or B |                 | 0.2<br>0.1   | mA      |
|          |                                      |                                                                                          |                  |                 |              |         |
| $I_{IH}$ | High Level Input<br>Current          | $V_{CC} = \text{Max}$<br>$V_I = 2.7V$                                                    | S or G<br>A or B |                 | 40<br>20     | $\mu A$ |
|          |                                      |                                                                                          |                  |                 |              |         |
| $I_{IL}$ | Low Level Input<br>Current           | $V_{CC} = \text{Max}$<br>$V_I = 0.4V$                                                    | S or G<br>A or B |                 | -0.8<br>-0.4 | mA      |
|          |                                      |                                                                                          |                  |                 |              |         |
| $I_{OS}$ | Short Circuit<br>Output Current      | $V_{CC} = \text{Max}$<br>(Note 6)                                                        | DM54<br>DM74     | -20<br>-20      | -100<br>-100 | mA      |
|          |                                      |                                                                                          |                  |                 |              |         |
| $I_{CC}$ | Supply Current                       | $V_{CC} = \text{Max}$ (Note 7)                                                           |                  | 4.8             | 8            | mA      |

**Note 5:** All typicals are at  $V_{CC} = 5V$ ,  $T_A = 25^\circ C$ .

**Note 6:** Not more than one output should be shorted at a time, and the duration should not exceed one second.



**Note 7:**  $I_{CC}$  is measured with 4.5V applied to all inputs and all outputs open.


## 'LS158 Switching Characteristics

at  $V_{CC} = 5V$  and  $T_A = 25^\circ C$


| Symbol           | Parameter                                          | From (Input)<br>To (Output) | R <sub>L</sub> = 2 kΩ  |     |                        |     | Units |
|------------------|----------------------------------------------------|-----------------------------|------------------------|-----|------------------------|-----|-------|
|                  |                                                    |                             | C <sub>L</sub> = 15 pF |     | C <sub>L</sub> = 50 pF |     |       |
|                  |                                                    |                             | Min                    | Max | Min                    | Max |       |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Data<br>to Y                |                        | 12  |                        | 18  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Data<br>to Y                |                        | 12  |                        | 21  | ns    |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Strobe<br>to Y              |                        | 17  |                        | 23  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Strobe<br>to Y              |                        | 18  |                        | 28  | ns    |
| t <sub>PLH</sub> | Propagation Delay Time<br>Low to High Level Output | Select<br>to Y              |                        | 20  |                        | 24  | ns    |
| t <sub>PHL</sub> | Propagation Delay Time<br>High to Low Level Output | Select<br>to Y              |                        | 24  |                        | 36  | ns    |

## Logic Diagrams






## Physical Dimensions inches (millimeters) unless otherwise noted



**Ceramic Leadless Chip Carrier Package (E)**  
**Order Number 54LS157LMQB or 54LS158LMQB**  
**Package Number E20A**


1/00A (REV D)




**16-Lead Ceramic Dual-In-Line Package (J)**  
**Order Number 54LS157DMQB, 54LS158DMQB, DM54LS157J or DM54LS158J**  
**Package Number J16A**

J16A (REV L)


**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)



**16-Lead Small Outline Molded Package (M)**  
Order Number DM74LS157M or DM74LS158M  
Package Number M16A



**16-Lead Molded Dual-In-Line Package (N)**  
Order Number DM74LS157N or DM74LS158N  
Package Number N16E



**16-Lead Ceramic Flat Package (W)**  
**Order Number 54LS157FMQB, 54LS158FMQB, DM54LS157W or DM54LS158W**  
**Package Number W16A**

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**Fairchild Semiconductor  
Corporation  
Americas**  
Customer Response Center  
Tel: 1-888-522-5372

**Fairchild Semiconductor**  
**Europe**  
Fax: +49 (0) 1 80-530 85 86  
Email: [europe.support@nsc.com](mailto:europe.support@nsc.com)  
Deutsch Tel: +49 (0) 8 141-35-0  
English Tel: +44 (0) 1 793-85-68-56  
Italy Tel: +39 (0) 2 57 5631

**Fairchild Semiconductor  
Hong Kong Ltd.**  
13th Floor, Straight Block,  
Ocean Centre, 5 Canton Rd.  
Tsimshatsui, Kowloon  
Hong Kong  
Tel: +852 2737-7200  
Fax: +852 2314-0061

**National Semiconductor  
Japan Ltd.**  
Tel: 81-3-5620-6175  
Fax: 81-3-5620-6179

[www.fairchildsemi.com](http://www.fairchildsemi.com)

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.