


© 1953 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



TONGUE MATERIAL THICKNESS = .045^{±.003}
FOR "A" MAX WIRE INS DIA

REVISIONS				
ZONE	LIP	DESCRIPTION	DATE	APPROVED
	C	REDRAWN & REVISED PG-5563 SR	1-5-70	Jme
	D	ADDED 2-322006-2 NPS 68-0656 (AE/12)	8-17-70	Jme
	E	REVISED REVISION D	9-15-70	FCY
	F	INACTIVATED 2-322006-1 P-7054 TR	6-7-73	Jme
	G	REV PER ECN P-7000 RB	11/23/79	-1-m
	H	OBSOLETE 2-1 P-9222 DDT	3-1-82	JSM
	J	REV G-4680 TMS	5-6-80	JT
	K	OBS. 2-2 PFR G-2693 JT	10/25/88	JT
	L	REV/0720-0060-93	4-6-93	TO /ml

TABLE I

20	LOOSE PC. BOX	8-322006-5	BODY: COPPER (QQ-C-576)
	WIRE TERMINAL	SEE TABLE II	FINISH: (SEE TABLE II)
			INSULATION: PVC COLOR: BLUE
			METALLIC SLEEVE: COPPER (QQ-C-576)
			METALLIC BAND: STEEL QQ-S-698 (ASTM A109)
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS: .008 ANGLES: 30°		CONTRACT NO.	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
MATERIAL		DR. J. Kautz 11-14-69	NAME
SEE TABLE I		CHK. Jm. Enominger 1-5-70	WIRE TERMINAL
		APPRO. Lwabel 1-7-70	AMPLI-BOND - RING TONGUE
		REL. Jm. Enominger 1-8-70	WIRE SIZE: 6
		DSGN APPD	SIZE B CODE IDENT NO. 00779 NUMBER 322006
		OTHER APPD	SCALE NTS SHEET 1 OF 1

TABLE II

8-322006-5	TIN PL (MIL-T-10727)	.377		
2-322006-2	TIN PL (MIL-T-10727)	.436		OBSOLETE
	GOLD PL (MIL-G-45204) TYPE II			
	00005 MIN EXT THK OVER			
2-322006-1	NICKEL PL (QQ-N-290) 00003	.377		OBSOLETE
	MIN. EXT. THK.			
322006	TIN PL (MIL-T-10727)		2-322006-3	
PART NO.	FINISH	"A"	PART NO. CUI TYPE	