






PRODUCT No.	ROWS	POWER		SIGNAL					POWER	
		E2	P2	6	5	4	3	2	P1	E1
51627-002-- NOTE: 2	D		PC	H	H	H	H	H	PA	
	C			G	G	G	G	G		
	B			F	F	F	F	F		
	A			E	E	E	E	E		



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PA	0.042	POWER
PC	0.092	POWER
E	N/A	SIGNAL
F	N/A	SIGNAL
G	N/A	SIGNAL
H	N/A	SIGNAL


mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com			
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3		projection		COPY	title			
A	DG06-0159	JMG	04/10/06		.XXX±.005/0.XX±0.13					IP + 24S + IP			
					.XXX±.0005/0.XXX±.051					RIGHT ANGLE SOLDER RECEPTACLE			
				angles	0°±2°			scale	1:1	product family		PwrBlade	code
				dr	JM GUO	04/10/06				size	dwg no	213	sheet 1 of 3
				enrg	SLUO	04/10/06							
				chr	BEER FU	04/10/06							
				appd	JOSEPH HSIA	04/10/06				A	51627-002		
sheet index	revision sheet	A	A	A									
		1	2	3									

A
FCI

A

B

PRODUCT NUMBER
51627-002--
NOTE: 2



RECOMMENDED PCB LAYOUT

CONFIDENTIAL

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lir	ecr no.	dr	date	linear		.XX±.01/0.X±0.3		COPY		title	
A						.XXX±.005/0.XX±0.13		projection		IP + 24S + IP	
						.XXXX±.0005/0.XXX±.051				RIGHT ANGLE SOLDER RECEPTACLE	
				angles		0°±2°		INCH/MM		product family	code
				dr	JM GUO	04/10/06		scale		PwrBlade	213
				enr	SLUO	04/10/06		1:1		size	sheet
				chr	BEER FU	04/10/06				51627-002	3
				appd	JOSEPH HSIA	04/10/06					
sheet index	revision	sheet									

Pro/E

PDM: Rev: A

STAT **Released**

Printed: Dec 20, 2010