

## VPS28-900

### Electrical Specifications (@25C)

1. Maximum Power: 25VA
2. Input Voltage: **Series**: 230VAC, 50/60Hz; **Parallel**: 115VAC, 50/60Hz
3. Output Voltage: **Series**<sup>1</sup>: 28V CT@ 0.9A; **Parallel**<sup>2</sup>: 14.0V @ 1.8A
4. Voltage Regulation: 25% TYP @ full load to no load
5. Temperature Rise: 30C TYP (45C MAX allowed)
6. Insulation Resistance: 100MΩ
7. Recommended Fuse<sup>3</sup>:
  - Series: Littelfuse p/n 313 1.0 HXP, 1A 250V, slow blow,  $\frac{1}{4}$  x  $1\frac{1}{4}$  or, Cooper Bussmann p/n BKMDL-1, 1A 250V,  $\frac{1}{4}$  x  $1\frac{1}{4}$
  - Parallel: Littelfuse p/n 313 2 HXP, 2A 250V, slow blow,  $\frac{1}{4}$  x  $1\frac{1}{4}$  or, Cooper Bussmann p/n BKMDL-2, 2A 250V,  $\frac{1}{4}$  x  $1\frac{1}{4}$

### Construction:

Dual bobbin construction with an insulated shroud, both made of a high temperature material that exceeds UL flammability requirements.

### Safety:

These units are designed with 4000VAC isolation between the primary and secondary, and also, between each winding and the core.

### Agency File:

UL: File E53148, UL 5085-1 and 2 (formerly UL 506), General Purpose.

File E65390, UL 5085-1 and 3 (formerly UL1585), Class 2/3

CSA: File LR 221330. C22.2 NO. 66, General Purpose.

TUV Certificate No.: R72103639, EN60950, Information Technology



### A. Dimensions:

H	W	D	A	B	C	T	Unit: In inches	
							MW	ML
2-5/16	2-13/16	1-15/16	2	1-1/8	5/16	3/16	2-3/8	-

B. Mounting Hole Size: 3/16"

C. WT Lbs. : 1.25

### Connections<sup>4</sup>:

**Input:** Series – 6 and 1, Jumper 5 to 2

Parallel – 6 and 1, Jumper 6 to 2 and 5 to 1

**Output:** Series – 12 and 7, Jumper 11 to 8

Parallel – 12 and 7, Jumper 12 to 8 and 11 to 7

**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.





\* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

<sup>1</sup> Inherently limited. Class 3.

<sup>2</sup> Non-Inherently limited. Class 2 not wet, Class 3 wet.

<sup>3</sup> Fuse must be used on **secondary** as conditions of acceptability for UL Class2/3 operation.

<sup>4</sup> Primary and secondary windings are designed to be connected in series or parallel. Winding are not intended to be used independently.



SCHEMATIC