







P.C.B. HOLE DRILLINGS (P.C.B. TOP SIDE)



NOTES:

1. RoHS COMPLIANT
2. FOR WAVESOLDERING (SOLDER BATH TEMPERATURE 260°C FOR 5 SEC. AND SOLDER PREHEAT 100°C FOR 30 SEC.)
3. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
4. INSULATOR: HIGH TEMPERATURE PLASTIC UL 94 V-0; BLACK
5. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
6. THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: Ø3,1 ± 0,1; PCB-THICKNESS 2,3mm
7. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. SEALING COMPOUND: PUR; BLUE
9. CAPACITANCE: 1300pF ± 20%
10. DIELECTRIC WITHSTANDING VOLTAGE: 707 VDC
11. CONNECTOR IS PART MARKED: FDC2XSRAA19H132X CONEC ABC



Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance			dim. in mm
rev.	description	date	name	date	name		
a	Origin			22.11.10	Henneboel		
				22.11.10	Fischer		

CONEC

scale:	2:1 (5:1)	
material:	SEE NOTES	
title:	D-SUB C-FILTER FEMALE 15pos. SOLDER PIN STRAIGHT with threaded spacer clip	
dwg no:	Inventor	DIN-A3
	24K1A1282	sh: 1
part no:	FDC2XSRAA19H132X	