



SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
	Sn63%, Pb37%	No	No
LF1	Sn96%, Ag4%	Yes	Yes

6G

more than you expect

Midcom



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

INDUCTANCE:	350uH min., 100kHz, 100mV, 8mADC, 16-15; 10-9, Lp.
DIELECTRIC RATING:	1500Vrms, 1 minute tested by applying 1800Vrms for 1 second between 1-16(tie 1+8, 9+16).
TURNS RATIO & POLARITY:	Per schematic.
INSERTION LOSS:	-1.0dB max., 300k - 125MHz.
RETURN LOSS:	-18dB min., 1M - 40MHz. -15dB min., 40M - 60MHz. -12dB min., 60M - 80MHz. -10dB min., 80M - 100MHz.
CROSSTALK:	-35dB min., 1M - 150MHz.
COMMON MODE REJECTION	-42dB min., 1M - 32MHz. -33dB min., 32M - 150MHz.
OPERATING TEMPERATURE RANGE:	0°C to +70°C.
COPLANARITY:	All 12 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.
Midcom p/n	000-7382-35R-LF1 is eiSos p/n: 749020100.

6D

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .005$ [.13]	DRAWING TITLE	PART NO.
6H	5/11	Method: Tape & Reel			TRANSFORMER AEDFP-G12	000-7382-35R/-LF1
6G	2/10	PKG-0362				
6F	8/08	www.we-online.com/midcom				
6E	6/08	SEE REVISION SHEET FOR REVISION LEVEL				
				This drawing is dual dimensioned. Dimensions in brackets are in millimeters. 6B	eiSos p/n: 749020100	SPECIFICATION SHEET 1 OF 1

