

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, — .

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC —

DIST —

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	25FEB11	GSK	RH
	B	ECR-13-005850	10APR2013	TB	PRO

NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND

2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1

3 WIRING SCHEDULE AS SHOWN

4. ASSEMBLY IN COLORS BLACK AND WHITE

F2

F3

F1

F4

VIEW A

A

3

2

1

4

3

2

1

4

2083135-1

2083135-1

L

3

2

1

4

3

2

1

4

2083135-1

2083135-1

B

3

2

1

4

3

2

1

4

F4

F1

F2

F3

VIEW B

FT

L

—

CABLE LIYY 4xAWG22 UL 2464 WH

4

FT

—

L

CABLE LIYY 4xAWG22 UL 2464 BK

4

PC

8

8

MICRO QUADLOK SYSTEM SOCKET CONTACT

3

PC

2

2

4 POS. LOW VOLTAGE CONN.M.POSITIONER

2

PC

—

2

4 POS. LOW VOLTAGE REC. CONN.HSG BK

1

PC

2

—

4 POS. LOW VOLTAGE REC. CONN.HSG WH

1

UOM

QTY

QTY

DECRPTION

POS.

2--X

1--X

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0

1

2

3

4

PLC

± —

1

2

3

4

PLC

± —

2

3

4

PLC

± —

3

4

PLC

± —

4

PLC

± —

ANGLES

± —

MATERIAL

—

FINISH

—

DWN
SATHISH KUMAR.G
25FEB2011

CHK
R.HOSSAINI

APVD
R.HOSSAINI

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

TE

TE Connectivity

NAME

CABLE ASSEMBLY NECTOR S LINE UL 4 POS.,
FEMALE TO FEMALE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2083135

—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
B

WIRING SCHEDULE 3

SIDE A	COLOR	SIDE B
F1	BN	F1
F2	RD	F2
F3	OG	F3
F4	BK	F4

PN	L/ft	TOLERANCES/ft
X-2083135-1	2	+0.06/-0.01
X-2083135-2	4	+0.07/-0.02
X-2083135-3	8	+0.10/-0.03
X-2083135-4	12	+0.12/-0.05
X-2083135-5	16	+0.17/-0.07

1470-19 (3/11)