







REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	05/10/12	L.CHAN




NON-SHIELDED
(8 POSITION, 8 CONTACTS SHOWN)



RECOMMENDED PANEL CUTOUT
SHIELDED





RECOMMENDED PANEL CUTOUT
NON-SHIELD



SHIELDED
(8 POSITION, 8 CONTACTS SHOWN)

FRJAE CONNECTOR NUMBER SYSTEM



RECOMMENDED P.C.B. LAYOUT

LOCATE HOLES
 $\phi .005$ [0.13]
POSITION DIMENSIONS
ARE BASIC

MATERIALS:
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
PLATING: 50 μ " [1.27 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ " [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
GOLD FLASH ON CONTACT TAILS.

SHIELD: COPPER ALLOY
PLATING: NICKEL WITH PURE-TIN DIPPED PCB TAIL.

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

DRAWN PAULW	DATE 05/12/25	Amphenol Canada Corp.		
DESIGNED				
CHECKED CHIGOW	05/12/25	TITLE FRJAE ASSEMBLY, 6 POSITION & 8 POSITION, WITH OR WITHOUT FERRITES, SINGLE PORT, HIGH TEMP. MATERIAL SHIELDED OR UNSHIELDED - RoHS COMPLIANT		
I. E. APPRD.				
Q. A. APPRD.		DWG DRAWING NO. P-FRJAE-XXX		REV. A
DWG. APPRD.				
ENG. REL. NO.		SCALE		SHEET 1 OF 1
REF.				
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554	WT. -----	SURF. -----	