



NOTES:
1. SUGGESTED MOUNTING HOLE = $\phi.147\pm.001$
2. MAX REFLOW IS 245°C FOR 5 SEC.



LEAD FINISH: SILVER	
EYELET FINISH: SILVER	
CAPACITANCE	22nF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C -- VDC MAX. 125°C 70 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	7
10	25
30	60
100	70
300	70
1 GHz	70



MARKING:
PART: NONE
BAG:
51F-750-302
DATE CODE
QTY./BAG (200 MAX.)

							03	02	01	00	REV. N.D.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api technologies corp. FAIRVIEW PENNSYLVANIA	
							CN #25162	CN 30515-CPD	CN 26049-CPD	CN 18049-CPD	CHANGE NOTICE	Fractions $\pm 1/64$	Dwn. KNOWLTON	Description
							REDRAWN					Dec. .xx $\pm$	Date 3-28-17	SOLDER MNT. FILTER
												Dec. .xxx $\pm .005$	ENGR. B.DEVINE	51F-750-302
												Angles $\pm 0^{\circ} 30'$	DO NOT SCALE	
												CODE IDENT. NO. 0LSP2		