

## IEC Appliance Inlet C14 with Fuseholder 1-pole



C14  
  
 70 °C

**Description**

- Panel Mount:  
Screw-on version from front or rear side, Appliance Inlet, Protection class I, Fuseholder for fuse-links 5 x 20 mm
- Solder terminals or quick connect terminals

**Approvals**

- UL File Number: E93617
- CSA File Number: 27324

**Characteristics**

- The fuse drawer "Fingergrip" can be removed by hand
- The fuseholder is accessible from the equipment front

**References**

We recommend for new applications the type [6200](#)


**Weblinks**

[pdf](#), [html](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

**Technical Data**

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| Ratings IEC               | 10A / 250VAC; 50Hz                                                |
| Ratings UL/CSA            | 10A / 250VAC; 60Hz                                                |
| Dielectric Strength       | > 3 kVAC between L-N<br>> 1.5 kVAC between L/N-PE<br>(1 min/50Hz) |
| Allowable Operation Temp. | -25 °C to 70 °C                                                   |
| Degree of Protection      | from front side IP 20 acc. to IEC 60529                           |
| Protection Class          | Suitable for appliances with protection class 1 acc. to IEC 61140 |
| Terminal                  | Solder terminals or quick connect terminals                       |
| Material: Housing         | PA6, black / grey / white, UL 94V-0                               |

|                              |                                                                                                                             |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Appliance Inlet              | C14 acc. to IEC/EN 60320-1<br>UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class 1 |
| Fuseholder                   | 1 or 2 pole, acc. to IEC 60127-6, for fuse-links 5 x 20 mm                                                                  |
| Power Acceptance @ Ta > 23°C | Admissible power acceptance at higher ambient temperature see derating curves                                               |

**Dimensions**

Length of the terminal please find at the order code configuration table

## Config. Code

## 1060 - H - A B C N - D - E G O

The characters are placeholders for the correspondingly keys of selections from the key tables.

## 1060 - H - A B C N - D - E G O = Type

| Type               | Configuration key |
|--------------------|-------------------|
| protection class 1 | X                 |

## 1060 - H - A B C N - D - E G O = Terminals

| Terminal L                         | Configuration key |
|------------------------------------|-------------------|
| short solder terminal (L = 4.8 mm) | 2                 |
| long solder terminal (L = 8.5 mm)  | 3                 |
| Blade terminal (4.8 x 0.8 mm)      | 8                 |
| Blade terminal (6.3 x 0.8 mm)      | 9                 |



## 1060 - H - A B C N - D - E G O = Terminals

| Terminal N                         | Configuration key |
|------------------------------------|-------------------|
| short solder terminal (L = 4.8 mm) | 2                 |
| long solder terminal (L = 8.5 mm)  | 3                 |
| Blade terminal (4.8 x 0.8 mm)      | 8                 |
| Blade terminal (6.3 x 0.8 mm)      | 9                 |

Symbols similar as in table A

## 1060 - H - A B C N - D - E G O = Terminals

| Terminal Ground                    | Configuration key |
|------------------------------------|-------------------|
| short solder terminal (L = 4.8 mm) | 2                 |
| long solder terminal (L = 8.5 mm)  | 3                 |
| Blade terminal (4.8 x 0.8 mm)      | 8                 |
| Blade terminal (6.3 x 0.8 mm)      | 9                 |

Symbols similar as in table A

## 1060 - H - A B C N - D - E G O = Terminal Fuseholder

| Terminal Fuseholder           | Configuration key |
|-------------------------------|-------------------|
| solder terminal               | 1                 |
| Blade terminal (4.8 x 0.8 mm) | 8                 |

## 1060 - H - A B C N - D - E G O = Color

| Color                | Configuration key |
|----------------------|-------------------|
| jet black; RAL9005   | A                 |
| silver grey; RAL7001 | B                 |
| pure white; RAL9010  | D                 |

## 1060 - H - A B C N - D - E G O = Style

| Style                         | Configuration key |
|-------------------------------|-------------------|
| flange with countersunk holes | 1                 |
| flange with through holes     | 2                 |

## 1060 - H - A B C N - D - E G O = Dimension X

| Dimension "X"                                                                                             | Configuration key |
|-----------------------------------------------------------------------------------------------------------|-------------------|
| 00                                                                                                        |                   |
| The dimension "X" is displayed in ( $\frac{1}{10}$ mm). This information is also valid for the order code |                   |

## 1060 - H - A B C N - D - E G O = Features

| Features                                               | Configuration key |
|--------------------------------------------------------|-------------------|
| dead cover                                             | 1                 |
| holder for 1 fuse (text legible, when inlet on top)    | 2                 |
| holder for 1 fuse (text legible, when inlet on bottom) | 3                 |

## Variants

| Config. Code       | Description                                                                                                                                                                                                                                                                                                                                                           | Order Number |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| 1060-X-2221-A-1002 | 1060, IEC Power Entry Module C14, 70°C, version: 1, L: short solder terminal (L = 4.8 mm), N: short solder terminal (L = 4.8 mm), ground: short solder terminal (L = 4.8 mm), fuseholder: solder terminal, color: jet black; RAL9005, design: flange with countersunk holes, dimension X: , features: holder for 1 fuse (text legible, when inlet on top), not used   | 4304.6005    |
| 1060-X-2221-B-1002 | 1060, IEC Power Entry Module C14, 70°C, version: 1, L: short solder terminal (L = 4.8 mm), N: short solder terminal (L = 4.8 mm), ground: short solder terminal (L = 4.8 mm), fuseholder: solder terminal, color: silver grey; RAL7001, design: flange with countersunk holes, dimension X: , features: holder for 1 fuse (text legible, when inlet on top), not used | 4304.6006    |
| 1060-X-8888-A-1002 | 1060, IEC Power Entry Module C14, 70°C, version: 1, L: Blade terminal (4.8 x 0.8 mm), N: Blade terminal (4.8 x 0.8 mm), ground: Blade terminal (4.8 x 0.8 mm), fuseholder: Blade terminal (4.8 x 0.8 mm), color: jet black; RAL9005, design: flange with countersunk holes, dimension X: , features: holder for 1 fuse (text legible, when inlet on top), not used    | 4304.6007    |
| 1060-X-8888-B-1002 | 1060, IEC Power Entry Module C14, 70°C, version: 1, L: Blade terminal (4.8 x 0.8 mm), N: Blade terminal (4.8 x 0.8 mm), ground: Blade terminal (4.8 x 0.8 mm), fuseholder: Blade terminal (4.8 x 0.8 mm), color: silver grey; RAL7001, design: flange with countersunk holes, dimension X: , features: holder for 1 fuse (text legible, when inlet on top), not used  | 4304.6008    |
| 1060-X-9998-A-1002 | 1060, IEC Power Entry Module C14, 70°C, version: 1, L: Blade terminal (6.3 x 0.8 mm), N: Blade terminal (6.3 x 0.8 mm), ground: Blade terminal (6.3 x 0.8 mm), fuseholder: Blade terminal (4.8 x 0.8 mm), color: jet black; RAL9005, design: flange with countersunk holes, dimension X: , features: holder for 1 fuse (text legible, when inlet on top), not used    | 4304.6009    |


The listed variants should be available from stock. Other versions on request [www.schurter.com/contact](http://www.schurter.com/contact)

## Packaging unit

50 Pcs

## Accessories

## Description



Assorted Covers  
Rear Cover

## Mating Outlets/Connectors

## Category / Description

## Connector Overview complete

|                                         |      |
|-----------------------------------------|------|
| IEC Connector C13, Rewireable, Angled   | 4012 |
| IEC Connector C13, Rewireable, Angled   | 4013 |
| IEC Connector C13, Rewireable, Straight | 4020 |
| IEC Connector C13, Rewireable, Angled   | 4021 |
| IEC Connector C13, Rewireable, Straight | 4022 |

Connector further types to 1060

...

## Interconnection Cord Overview complete

|                                    |           |
|------------------------------------|-----------|
| Interconnection Cord C13/C14, 10 A | 6007.0212 |
|------------------------------------|-----------|

Interconnection Cord further types to 1060

## Power Cord Overview complete

|                                           |      |
|-------------------------------------------|------|
| Power Cord with IEC Connector C13, Angled | 0311 |
| Power Cord with IEC Connector C13, Angled | 3011 |
| Power Cord with IEC Connector C13, Angled | 3012 |
| Power Cord with IEC Connector C13, Angled | 3013 |
| Power Cord with IEC Connector C13         | 3020 |

Power Cord further types to 1060

...

## Category / Description

[Power Supply CordOverview complete](#)

|                                                       |           |
|-------------------------------------------------------|-----------|
| EU Power Supply Cord with IEC Connector C13, straight | 6003.0215 |
| EU Power Supply Cord with IEC Connector C13, straight | 6004.0215 |
| CH Power Supply Cord with IEC Connector C13, straight | 6011.0215 |
| IT Power Supply Cord with IEC Connector C13, straight | 6026.0215 |
| UK Power Supply Cord with IEC Connector C13, straight | 6043.0114 |

[Power Supply Cordfurther types to1060](#)

...

[Power Supply or Interconnection CordOverview complete](#)

|                                                                 |           |
|-----------------------------------------------------------------|-----------|
| Power Supply Cord with IEC Connector C13 straight, stripped end | 6000.0214 |
| Power Supply Cord with IEC Connector C13 angled, stripped end   | 6000.0224 |
| Divers Power Supply and Interconnection Cords 10 A              | 6003.0204 |
| Divers Power Supply and Interconnection Cords 10 A              | 6003.0205 |
| Interconnection Cord C13/C14, 10 A                              | 6007.0214 |

[Power Supply or Interconnection Cordfurther types to1060](#)

...