


A: MATERIAL
 1. HOUSING: THERMOPLASTIC
 2. TERMINAL: COPPER ALLOY
B: CHARACTERISTICS:
 1. RATING: 16A 250V AC/ 20A 125V AC
 2. INSULATION RESISTANCE:>100M OHM 500VDC
 3. DIELECTRIC STRENGTH:2000V ONE MINUTE
C: APPROVALS:
 UL, CSA,VDE,SEV,SEMKO,FIMKO & NEMKO
D: OPTION GUIDE:

Revision			
Rev.	Description	Date	Approved

PART NO.	ITEM	TERMINAL DIFFERENCE
745W-XX/PP	1+2	Solder Terminal 2.8X0.8 mm
745W-XX/QQ	1+3	Solder Terminal 4.0X0.8 mm
745W-XX/RR	1+4	Quick Con. Terminal 4.8X0.8mm
745W-XX/SS	1+5	Quick Con. Terminal 6.3X0.8mm
"XX" Panel Thickness (A) in 1/10 mm		
PP: 01,05,09,13,17 QQ:02,06,10,14,18		
RR: 03,07,11,15,19 QQ:04,08,12,16,20		
745W-15/05:Panel thickness 1.5mm terminal 2.8mm		



Dim range (mm)		Tolerance +/- (mm)		Qualtek Electronics Corp. PPC DIVISION		
0-1		0.15		Part Number: 745W SERIES		
1-6		0.20		Description: AC RECEPTACLES		
6-18		0.30				
18-50		0.50				
50-120		0.70				
120-250		0.90				
250-500		1.20				
				Drawn/Date	Checked/Date	Approved/Date
				K.Huang	11-21-98	JJH/11-21-98
				11-21-98		